



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 22SRLD229CUNVL84 SR 2X2 Led Layin 4000K 2900LM *Cooper Lighting Solutions*

Catalog Number	22SRLD229CUNVL84
Manufacturer	Cooper Lighting Solutions
Description	Led, 2'X2' Skyridge, Wavestream, 2900 Lumens, 85 Cri, 4000K, Unv 0-10V Dimming Driver, Curved.
Weight per unit	14.6 (lbs/each)
Product Category	Lighting

### Features

amperage rating	0.084 at 277V
Ballast Type	N/A
Lamp Type	LED
Material	Aluminum
Number of Lamps	1
Socket Type	N/A
Voltage Rating	120/277V

### Material, Color, and Finish

Style	(blank)
-------	---------

### Descriptions

Description	22SRLD229CUNVL840CD1U
extra long description	CLS 22SR-LD2-29-C-UNV-L840-CD1-U 2X
Long Description	LED, 2'x2' SkyRidge, WaveStream, 2900 Lumens, 85 CRI, 4000K, UNV 0-10V Dimming Driver, Curved.
Product Type	2X2 Led Sky RDG, 2900, 40K, Unv 0-10V DD
Special Features	Available in 1' x 2', 1' x 4', 2' x 2' and 2' x 4' recessed versions

### Manufacturer Information

Brand	METALUX SPECIFICATION
GTIN	00080083752577
Manufacturers Part Number	22SR-LD2-29-C-UNV-L840-CD1-U
UPC	080083752577

### Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Recessed Static

### Packaging

Carton	1
Weight Per each	14.6



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	lighting
Mounting	Recessed
standard	UL Recognized;cULus Listed;LM79/LM80 Compliant;DLC Qualified;IC Rated;RoHS Compliant;Damp Locations Listed;NOM Certified;25 Degree C Ambient Temperature Rating