



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



23447 14/4 SJ Yellow 300V

Southwire Company

Catalog Number	23447
Manufacturer	Southwire Company
Description	Portable Cord, Sjeoow Type; 250 FT; 0.4 Inch Outer Diameter; Bare Copper Conductor Material; UI 62, Csa C22.2, Msha Approval
Weight per unit	0.1030 (lbs/ft)
Product Category	Sjeow-Sjeoow

Features

Conductor Size	14 AWG
Number of Conductors	4
Stranding	41/30 STRANDS
Voltage Rating	300 V

Material, Color, and Finish

Color Code	BLACK, WHITE, RED, GREEN
Conductor Material	Bare Copper
Insulation Material	T-Prene Thermoplastic Elastomer
Jacket Color	YELLOW
Jacket Material	Chemical/Oil/Water Resistant Seoprene Thermoplastic Elastomer

Dimensions and Weight

Length	250 ft
Outer Diameter	0.4 INCH



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Additional Information	ROHS Compatible; Applicable Standard NEC 400, Federal Specification JC-580; Current Rating 15 Ampere; Insulation Thickness 0.03 Inch
Commodity Description	SJEOW - SJEOOW - 300V CORD & CABLE
Description	14/4 SJ YELLOW 300V
extra long description	SJEOOW TYPE; 250 FT; 0.4 INCH OUTER DIAMETER; BARE COPPER CONDUCTOR MATERIAL; UL 62, CSA C22.2, MSHA APPROVAL; INDUSTRIAL CONTROL, MOTOR CONTROL, MINING, PORTABLE POWER DISTRIBUTION, PUSHBUTTON REMOTE CONTROL, ROBOTIC SYSTEM, STAGE EQUIPMENT, LIGHTING APPLICATION; 300 V VOLTAGE RATING; -50 TO 105 DEG C TEMPERATURE RATING; 4 CONDUCTOR(S); T-PRENE THERMOPLASTIC ELASTOMER INSULATION MATERIAL; 14 AWG CONDUCTOR SIZE; BLACK, WHITE, RED, GREEN COLOR CODE; CHEMICAL/OIL/WATER RESISTANT SEOPRENE THERMOPLASTIC ELASTO
Long Description	PORTABLE CORD, SJEOOW TYPE; 250 FT; 0.4 INCH OUTER DIAMETER; BARE COPPER CONDUCTOR MATERIAL; UL 62, CSA C22.2, MSHA APPROVAL
Product Type	Portable Cord

Manufacturer Information

Brand	Cables & Cords
Manufacturers Part Number	55818801
Model	234

Taxonomies, Classifications, and Categories

Category Description	Portable Cords, Voice, Data, Video Wire & Cable
Type	SJEOOW

Packaging

Carton	250
Package Type	Reel
Weight Per foot	0.103

Uses, Certifications, and Standards

Application	Industrial Control, Motor Control, Mining, Portable Power Distribution, Pushbutton Remote Control, Robotic System, Stage Equipment, Lighting
Approval	UL 62, CSA C22.2, MSHA
Temperature Rating	-50 TO 105 DEG C