



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 24248SCG Type 3 GLV Gasketed SC 24

*Cooper B-Line/Cable Tray*

Catalog Number	24248SCG
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Type 3/3R Junction Boxes, 24" Height, 8" Length, 24" Width, Nema 3 and 12, Screw Cover, SCG Enclosure, Surface Mounted, Medium Single Door, No Mounting Provisions, Galvanized Steel, Oil-Resistant Gasket, Gasketed Screws
Weight per unit	52.8 (lbs/each)
Product Category	Nema Types 3 & 3R Metallic Enc

### Features

dimensions	8.0000 IN X 24.0000 IN X 24.0000 IN
Material	Galvanized Steel
Mounting Type	Surface

### Material, Color, and Finish

Color	Gray
-------	------

### Dimensions and Weight

Size	24.00 In Width X 8.00 In Depth X 24.00 In Height
------	--

### Descriptions

Description	TYPE 3 GLV GASKETED SC 24
extra long description	B-LINE 24248 SCG TYPE 3 GLV GASKETE
Features	Eaton's B-Line series junction boxes provide reliable environmental protection and are used as commercial wiring, junction, pull, and termination boxes.
Long Description	Eaton B-Line series Type 3/3R junction boxes, 24" height, 8" length, 24" width, NEMA 3 and 12, Screw cover, SCG enclosure, Surface mounted, Medium single door, No mounting provisions, Galvanized steel, Oil-resistant gasket, gasketed screws
Product Type	Type 3 GLV Gasketed SC 24X24X8

### Manufacturer Information

Brand	Eaton
GTIN	00782051108798
Manufacturers Part Number	24248 SCG
UPC	782051108798

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Type 3/3R junction boxes



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	52.8

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Building Automation and Monitoring Commercial / Institutional Buildings / Structures - Commercial/Inst Bldg Structures - Aftermarket Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other Commercial / Institutional Buildings / Structures - Critical Power Aviation Commercial / Institutional Buildings / Structures - Power Distribution and Controls Commercial / Institutional Buildings / Structures - Safety and Security Systems Commercial / Instituti
nema rating	312
standard	CSA C22.2, NEMA, UL 50