



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



25630695593 1/0AWG, 1/2" STD 2H, 1-3/4" SPC Cu CMP Lug

Abb Installation Products, Inc

| | |
|------------------|---|
| Catalog Number | 25630695593 |
| Manufacturer | Abb Installation Products, Inc |
| Description | Copper Two-Hole Lug, Long Barrel, Blind End, Max 35KV, Wire Size 1/0 Awg, 1/2 Inch Bolt Size, 1-3/4 Inch Hole Spacing, Tin Plated, Die Color Code Pink, Die Code 42 |
| Weight per unit | 0.1090 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|-----------------|---------|
| Cable Size | 1/0 AWG |
| insulation | None |
| Material | Copper |
| Number of Holes | 2 |
| Stud Size | 1/2 in |
| Voltage Rating | 35 kV |

Material, Color, and Finish

| | |
|-------|------|
| Color | Pink |
|-------|------|

Descriptions

| | |
|------------------------|---|
| Description | 1/0AWG,1/2" STD 2H,1-3/4" SPC CU CMP LUG |
| extra long description | ABB 256-30695-593 CU TP 2HL LUG LON |
| Long Description | Copper Two-Hole Lug, Long Barrel, Blind End, Max 35kV, Wire Size 1/0 AWG, 1/2 Inch Bolt Size, 1-3/4 Inch Hole Spacing, Tin Plated, Die Color Code Pink, Die Code 42 |
| Product Type | Cu TP 2HL Lug Longbrl 1/0 1/2B PNK |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | COLOR-KEYED |
| GTIN | 00786210071404 |
| Manufacturers Part Number | 256-30695-593 |
| UPC | 786210071404 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | Long Barrel |

Packaging

| | |
|-----------------|-------|
| Carton | 5 |
| Package | 25 |
| Weight Per each | 0.109 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

UL E9809
