

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

805 South Timberlane Drive 71730-0000, AR El Dorado Phone: 870-639-6289 Fax: 870-864-8850



25DTPE10 Tele-Power Express Pole (2) 5' Wiremold/Legrand

Catalog Number	25DTPE10
Manufacturer	Wiremold/Legrand
Description	<p>Two Sections Of A Two-Compartment (Power and Communication) Pole (5'4"" (1.626M) Base + 5' (1.524M) Extender) Assembles to Form A 10' 4"" (3.148M) Pole. Nominal Material Thickness .040"" (1.0MM). Ivory or Gray Boot Base. Factory Wired With Fed-Spec General Grade 20A 125V Duplex Style Receptacles. An 8"" (203MM) Cover At Top Front (Power Side) Of Pole Is Removable For Making Power Wiring Connections. Kos Provided In Removable Cover For RJ11/RJ45 and Modular Furniture Communication Connectors. Mounting Ha</p>
Weight per unit	22.0 (lbs/each)
Product Category	Telephone/Power Poles
Features	
cutout	Receptacle, Data, Keystone, A/V
Material	Steel
Number of Channels	2.0
Material, Color, and Finish	
Color	lvory



ELLIOTT ELECTRIC SUPPLY We Deliver Lower Cost, Quality Products, & Personal Service 805 South Timberlane Drive 71730-0000, AR El Dorado Phone: 870-639-6289 Fax: 870-864-8850

Descriptions	TELE DOWNED EVEDESS DOLE (2) EL
Description	TELE-POWER EXPRESS POLE (2) 5' WM 25DTP-E10 TELE-POWER EXPRESS POL
extra long description Features	Two sections of a two-compartment (power and)
reatures	communication) pole (5'4"" (1.626m) base + 5' (1.524m)
	extender) assembles to form a 10' 4"" (3.148m) pole. Nominal
	material thickness .040"" (1.0mm). Ivory or gray boot base. Factory wired with fed-spec general grade 20A 125V duplex style receptacles. An 8"" (203mm) cover at top front (power side) of pole is removable for making power wiring connections. KOs provided in removable cover for RJ11/RJ45 and modular furniture communication connectors. Mounting ha
Long Description	Two sections of a two-compartment (power and
	communication) pole (5'4"" (1.626m) base + 5' (1.524m) extender) assembles to form a 10' 4"" (3.148m) pole. Nominal material thickness .040"" (1.0mm). Ivory or gray boot base. Factory wired with fed-spec general grade 20A 125V duplex style receptacles. An 8"" (203mm) cover at top front (power side) of pole is removable for making power wiring connections. KOs provided in removable cover for RJ11/RJ45 and modular furniture communication connectors. Mounting ha
Product Type	Tele-Power Express Pole (2)5FT
Special Features	Bring power, data, and A/V services into open
	spaceenvironments quickly & easily. Custom capabilities. On-site configurability. A/V Compatibility. Datacom connectivity options.
Manufacturer Information	
Brand	WIREMOLD
GTIN	00786776172539
Manufacturers Part Number	25DTP-E10
UPC	786776172539
Taxonomies, Classifications, and Cate	gories
Category Description	Panduit & Wiremold Metallic & Non-Metallic Raceways
Туре	Pole
Packaging Carton	1
Weight Per each	22
Uses, Certifications, and Standards	
standard	ROHS, CULUS, cULus Listed, Multioutlet Assemblies: File E15191, E178348