



Search Milwaukee tool.com

Home > Products > Tools > Cordless Tools > M18™ Cordless LITHIUM-ION System > HACKZALL® M18™ Cordless LITHIUM-ION One-Handed Recip Saw Kit

SHARE

PRINT

## HACKZALL® M18™ Cordless LITHIUM-ION One-Handed Recip Saw Kit 2625-21

Buy Local

Zip Code



BUY ONLINE

Related Items



Photos

Videos

### The Milwaukee Advantage

The HACKZALL® M18™ Cordless LITHIUM-ION One-Handed Recip Saw (2625-20) features a Patent Pending Dual Gear Anti-Vibration System for unmatched comfort and control as well as light weight design for superior control and versatility. The powerful motor delivers 0-3,000 strokes per minute and a 3/4" stroke length allows for fast cutting through a wide range of material such as wood, metal and PVC. The dual gear anti-vibration system increases control and accuracy. The 2625-21 also features a QUIK-LOK® blade clamp which offers fast and easy blade changes.

### Features

One-handed design provides superior control & versatility over a standard reciprocating saw

Compact size allows for cutting in tight spaces, and light weight makes overhead work easier QUIK-LOK® Blade Clamp offers fast, easy tool free blade changes for SAWZALL® Blades & HACKZALL® Blades

Built-In LED light illuminates the work surface while cutting  
Compatible with M18™ XC High Capacity REDLITHIUM™ Batteries and M18™ Compact REDLITHIUM™ Batteries

### Specifications

Voltage	18V
Speed	0-3000 SPM
Stroke Length	¾"
Blade Clamp	QUIK-LOK™ Universal
Trigger	Variable
Battery	LITHIUM-ION
Tool Length	13 in
Tool Weight	4.1 lbs
Shipping Weight	9.87 lbs

### Includes

- 2625-20 HACKZALL® M18™ Cordless LITHIUM-ION One-Handed Recip Saw
- (1) M18™ XC High Capacity REDLITHIUM™ Battery
- 1-Hour Charger
- SAWZALL® Blade
- Contractor Bag



6" 18 TPI Sawzall® Blades (50 Pk)



M12 Hackzall™ Blade-10 PC. Set



M18™ XC High Capacity REDLITHIUM™ Battery

+ [More Related Items](#)

Related Articles

[Milwaukee® Introduces New Hackzall® M18™ Cordless One-Handed Recip Saw](#)

Sign Up for the Heavy Duty Club



Products

New Products & Offers  
Tools  
Accessories

Parts & Service

e-SERVICE Tool Repair  
Test & Measure Service  
Find a Service Center

News & Media

Press Releases  
Milwaukee Ink  
MilwaukeeCain.com

About Us

Milwaukee Story  
Careers  
Locations

SUBMIT >

Test & Measurement  
Milwaukee Gear  
Print Current Catalog

Download Manuals  
Parts Pricing  
Milwaukee Warranty  
Lightning Max Repair  
FAQ's

Product Reviews  
Media Center  
Media Inquiries

[Buy Now](#)  
[Contact Us](#)



Search Milwaukee tool.com

Home > Products > Tools > Cordless Tools > M18™ Cordless LITHIUM-ION System > HACKZALL® M18™ Cordless LITHIUM-ION One-Handed Recip Saw Kit

SHARE

PRINT

## HACKZALL® M18™ Cordless LITHIUM-ION One-Handed Recip Saw Kit 2625-21

Buy Local

Zip Code



BUY ONLINE

Related Items



Photos

Videos

### The Milwaukee Advantage

The HACKZALL® M18™ Cordless LITHIUM-ION One-Handed Recip Saw (2625-20) features a Patent Pending Dual Gear Anti-Vibration System for unmatched comfort and control as well as light weight design for superior control and versatility. The powerful motor delivers 0-3,000 strokes per minute and a 3/4" stroke length allows for fast cutting through a wide range of material such as wood, metal and PVC. The dual gear anti-vibration system increases control and accuracy. The 2625-21 also features a QUIK-LOK® blade clamp which offers fast and easy blade changes.

### Features

One-handed design provides superior control & versatility over a standard reciprocating saw

Compact size allows for cutting in tight spaces, and light weight makes overhead work easier QUIK-LOK® Blade Clamp offers fast, easy tool free blade changes for SAWZALL® Blades & HACKZALL® Blades

Built-In LED light illuminates the work surface while cutting  
Compatible with M18™ XC High Capacity REDLITHIUM™ Batteries and M18™ Compact REDLITHIUM™ Batteries

### Specifications

Voltage	18V
Speed	0-3000 SPM
Stroke Length	¾"
Blade Clamp	QUIK-LOK™ Universal
Trigger	Variable
Battery	LITHIUM-ION
Tool Length	13 in
Tool Weight	4.1 lbs
Shipping Weight	9.87 lbs

### Includes

- 2625-20 HACKZALL® M18™ Cordless LITHIUM-ION One-Handed Recip Saw
- (1) M18™ XC High Capacity REDLITHIUM™ Battery
- 1-Hour Charger
- SAWZALL® Blade
- Contractor Bag



6" 18 TPI Sawzall® Blades (50 Pk)



M12 Hackzall™ Blade-10 PC. Set



M18™ XC High Capacity REDLITHIUM™ Battery

+ [More Related Items](#)

Related Articles

[Milwaukee® Introduces New Hackzall® M18™ Cordless One-Handed Recip Saw](#)

Sign Up for the Heavy Duty Club



#### Products

New Products & Offers  
Tools  
Accessories

#### Parts & Service

e-SERVICE Tool Repair  
Test & Measure Service  
Find a Service Center

#### News & Media

Press Releases  
Milwaukee Ink  
MilwaukeeCain.com

#### About Us

Milwaukee Story  
Careers  
Locations

SUBMIT >

Test & Measurement  
Milwaukee Gear  
Print Current Catalog

Download Manuals  
Parts Pricing  
Milwaukee Warranty  
Lightning Max Repair  
FAQ's

Product Reviews  
Media Center  
Media Inquiries

[Buy Now](#)  
[Contact Us](#)