

M18™ Cordless LITHIUM-ION 5-3/8" Metal Saw Kit 2682-22

[PRINT](#)[Tweet](#)

998

[Share](#)

3392

[ShareThis](#)

4481

NEW


 0.0
Be the first to [Write a Review](#)

Milwaukee Electric Tool Corporation introduces the new M18™ Cordless LITHIUM-ION 5-3/8" Metal Saw. This compact and lightweight metal cutting saw delivers the fastest cuts for the electrical, mechanical, plumbing, HVAC and general construction contractor. The 2682 utilizes an exclusive 4-Pole Frameless Motor for up to 35% more cutting power and best in class run-time with over 200 cuts of 3/4" EMT per charge.

The Milwaukee M18™ Cordless LITHIUM-ION 5-3/8" Metal Saw features a

[SHOW MORE](#)

Includes

- M18™ Cordless LITHIUM-ION 5-3/8" Metal Saw
- (2) M18™ XC High Capacity RED LITHIUM™ Battery Packs
- 1-Hour Charger
- 30T METAL TECH™ Carbide-Tipped Blade,
- Blade Wrench
- Contractor Bag

[FIND RETAILERS](#)


FEATURES


- Exclusive 4-Pole Frameless Motor delivers up to 35% more cutting power
- Compact, low-profile design for easy handling and increased control
- Extra-Large cut guide, impact resistant window and LED light for more accurate cuts
- Lightweight 5.8 lbs design for easier overhead cuts and less user fatigue
- Superior Cut Quality - 30T METAL TECH™ Carbide-Tipped blade produces cool, burr-free cuts through EMT, strut, threaded rod, sheet metal, angle iron and other ferrous materials.
- Tool-Free Depth Adjustment quickly and easily adjusts cutting depth from 1/8"-2"

SPECIFICATIONS

Voltage	18V
Speed	3600 RPM
Cut Capacity	1/8" - 2"
Arbor	20mm
Blade Size	5-3/8" 30T Carbide-Tipped (50T 5-3/8" Carbide-Tipped Also Available)
Battery	M18™ Compact or XC High Capacity RED LITHIUM™ Battery Packs
Batteries Included	(2) M18™ XC High Capacity RED LITHIUM™ Battery Packs
Shoe	Stainless Steel
Width	6.5"
Trigger	Lock Off
Blade Guard	Polycarbonate
Tool Length	14"
Tool Weight	4.3 lbs
Tool Weight (w/battery)	5.8 lbs
Shipping Weight	10.7 lbs

RELATED ARTICLES

 [Milwaukee M18 Cordless 5-3/8" Metal Saw Preview Review](#)

 [Milwaukee® Introduces Cordless Metal Saw with 35% More Power](#)

REVIEW SNAPSHOT® by PowerReviews

Not yet rated. Be the first to [Write a Review](#)

RELATED ITEMS



5-3/8" 30T Ferrous Metal Blade



5-3/8" 50T Non-Ferrous Metal Blade



M18™ XC High Capacity RED LITHIUM™ Battery

[MORE RELATED ITEMS](#)

Find us on Facebook



Milwaukee Electric Tool



6,401 people like **Milwaukee Electric Tool**.



Sean



Adam



Jake



Mikael



José G.



Kevin



Jeffrey



Joseph

 Facebook social plugin

Sign Up for the Heavy Duty Club



[SUBMIT ▶](#)

Products

[New Products & Offers Tools](#)
[Accessories](#)
[Test & Measurement](#)
[Milwaukee Gear](#)
[Print Current Catalog](#)

Parts & Service

[e-SERVICE Tool Repair](#)
[Test & Measure Service](#)
[Find a Service Center](#)
[Download Manuals](#)
[Parts Pricing](#)
[Milwaukee Warranty](#)
[Lightning Max Repair](#)
[FAQ's](#)

News & Media

[Press Releases](#)
[MilwaukeeCain.com](#)
[Product Reviews](#)
[Media Center](#)
[Media Inquiries](#)

About Us

[Milwaukee Story](#)
[Careers](#)
[Locations](#)
[Buy Now](#)
[Contact Us](#)