



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 271920 M18 Fuel Hackzall (Tool Only)

*Milwaukee Electric Tool*

Catalog Number	271920
Manufacturer	Milwaukee Electric Tool
Description	The Milwaukee 2719 M18 Fuel™ Hackzall® Is The Fastest Cutting and Most Powerful One-Handed Reciprocating Saw. Utilizing A Powerstate Brushless Motor and A Best In Class 7/8 In. Stroke Length, The M18 Fuel™ Hackzall® Cuts Up to 50% Faster Than Competitors. The Compact, One-Handed Design Provides Superior Control and The Ability to Make Cuts In Tight Spaces. The Dual Gear Counter Balance Mechanism Provides Up to 4X Lower Vibration Than Traditional Reciprocating Saws, Resulting In Faster Cut-Starts In Metal A
Weight per unit	4.6 (lbs/each)
Product Category	Battery Driven Tools

### Features

Battery Voltage	18
media	Yes
Stroke Length	0.875

### Material, Color, and Finish

Housing Material	Glass Filled Nylon
------------------	--------------------

### Dimensions and Weight

Height	7
Length	14
Width	3.31



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	M18 FUEL HACKZALL (TOOL ONLY)
extra long description	MILW 2719-20 Reciprocating Saw
Features	Milwaukee Tool is committed to protecting our users's investments by providing high performing, trade-focused solutions that are fully compatible with M18™ REDLITHIUM™ batteries. The M18™ system has over 200 performance-driven solutions, and growing!
Long Description	The Milwaukee 2719 M18 FUEL™ HACKZALL® is the fastest cutting and most powerful one-handed reciprocating saw. Utilizing a POWERSTATE brushless motor and a best in class 7/8 in. stroke length, the M18 FUEL™ HACKZALL® cuts up to 50% faster than competitors. The compact, one-handed design provides superior control and the ability to make cuts in tight spaces. The dual gear counter balance mechanism provides up to 4x lower vibration than traditional reciprocating saws, resulting in faster cut-starts in metal a
Product Type	Reciprocating Saw

## Manufacturer Information

Brand	Milwaukee®
GTIN	00045242502776
Manufacturers Part Number	2719-20
UPC	045242502776

## Taxonomies, Classifications, and Categories

Category Description	POWER TOOLS
----------------------	-------------

## Packaging

Carton	1
Package	6
Weight Per each	4.57