



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



271722HD M18 Fuel 1-9/16" SDS Max Hammer Drill Kit

Milwaukee Electric Tool

| | |
|------------------|---|
| Catalog Number | 271722HD |
| Manufacturer | Milwaukee Electric Tool |
| Description | The Milwaukee® M18 Fuel™ 1-9/16" SDS Max Rotary Hammer Is The First to World 18V SDS Max Cordless Solution. By Utilizing Proprietary M18™ and M18 Fuel™ Technologies, The 1-9/16" SDS Max Rotary Hammer Is Able to Drill As Fast As A Corded SDS Max Rotary Hammer, Deliver Corded Durability, and Provide Over 20 Minutes Of Continuous Chipping. Powerstate™ Brushless Motor Delivers 5 FT-LBS Of Impact Energy For The More Demanding, Heavy-Duty Applications. Including Dry Coring and Medium Duty Chipping In Both Concre |
| Weight per unit | 34.9 (lbs/each) |
| Product Category | Bits, Parts, Accessories |

Features

| | |
|-----------------|----------------|
| Battery Voltage | 18 |
| Chuck Capacity | 1-9/16 SDS-Max |
| Switch Type | Trigger |

Material, Color, and Finish

| | |
|------------------|--------------------|
| Handle Material | Rubber |
| Housing Material | Glass Filled Nylon |

Dimensions and Weight

| | |
|-------|-----|
| Width | 3.9 |
|-------|-----|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--|
| Description | M18 FUEL 1-9/16" SDS MAX HAMMER DRILL KIT |
| extra long description | MILW 2717-22HD Hammer Drill Kit |
| Features | Milwaukee Tool is committed to protecting our users's investments by providing high performing, trade-focused solutions that are fully compatible with M18™ REDLITHIUM™ batteries. The M18™ system has over 200 performance-driven solutions, and growing! |
| Long Description | The MILWAUKEE® M18 FUEL™ 1-9/16" SDS Max Rotary Hammer is the first to world 18V SDS Max cordless solution. By utilizing proprietary M18™ and M18 FUEL™ technologies, the 1-9/16" SDS Max rotary hammer is able to drill as fast as a corded SDS Max rotary hammer, deliver corded durability, and provide over 20 minutes of continuous chipping. POWERSTATE™ Brushless Motor delivers 5 ft-lbs of impact energy for the more demanding, heavy-duty applications. Including dry coring and medium duty chipping in both concrete. |
| Product Type | Hammer Drill Kit |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Milwaukee® |
| GTIN | 00045242356775 |
| Manufacturers Part Number | 2717-22HD |
| UPC | 045242356775 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------|
| Category Description | POWER TOOLS |
|----------------------|-------------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Weight Per each | 34.938 |