



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 28W75 Turnlok Plug IP67 30A 3PH 250V L1530P

*Pass & Seymour/Legrand*

|                  |   |
|------------------|---|
| Catalog Number   | 28W75   |
| Manufacturer     | Pass & Seymour/Legrand  |
| Description      | Locking Watertight Plug, 30AMP 3 250 Volt, Nema Configuration L15-30, Multipoint Sealing System Provides Environmental Protection Of: Nema 4, 4X, 6, 6P and IP67 Rated. |
| Weight per unit  | 0.5800 (lbs/each)   |
| Product Category | Plugs, Connectors, Inlets, Out  |

### Features

|                 |   |
|-----------------|---|
| amperage rating | 30  |
| Cord Type       | 12/4 S to 8/4 S, 6/4 MSHA, .640" min to .930" max |
| Material        | Rubber  |
| Number of Wires | 4   |
| Phase           | 3   |
| Poles           | 3-way   |
| Voltage Rating  | 250   |
| Wire Size       | 12-6  |

### Descriptions

|                        |  |
|------------------------|--|
| Description            | TURNLOK PLUG IP67 30A 3PH 250V L1530P  |
| extra long description | P&S 28W75 TL PLUG IP67 30A 3PH 250V  |
| Long Description       | Locking Watertight Plug, 30amp 3 250 volt, NEMA Configuration L15-30, multipoint sealing system provides environmental protection of: NEMA 4, 4X, 6, 6P and IP67 rated.  |
| Product Type           | TL Plug IP67 30A 3PH 250V L1530P   |
| Special Features       | Rated watertight for 1,500 psi high-pressure hosedown, P&S Turnlok® watertight plugs & connectors feature rugged construction, multiple seals to ensure protection against the environment and ease of installation. |

### Manufacturer Information

|                           |                        |
|---------------------------|------------------------|
| Brand                     | LEGRAND-PASS & SEYMOUR |
| GTIN                      | 00785007033267         |
| Manufacturers Part Number | 28W75                  |
| UPC                       | 785007033267           |

### Taxonomies, Classifications, and Categories

|                      |                         |
|----------------------|-------------------------|
| Category Description | Residential receptacles |
| Type                 | LOCKING PLUG            |

### Trade Size

|          |      |
|----------|------|
| Amperage | 30.0 |
|----------|------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 10   |
| Weight Per each | 0.58 |

## Uses, Certifications, and Standards

|                          |   |
|--------------------------|---|
| Application              | High-pressure washdowns. Particle build-up. Condensation. Corrosive substances. Food and beverage processing plants can be harsh, challenging environments. Fortunately, we have a full menu of electrical devices that keep things running smoothly while protecting people and equipment. IEC PIN & SLEEVE DEVICES Watertight Plugs & Connectors   Thermoplastic elastomer body resists water, oils, lubricants and soaps while maintaining NEMA 4, 4X, 6, 6P, and IP65, 66, 67 ratings   Ideal for washdown areas — rated wa |
| environmental conditions | Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized  |
| nema rating              | L15-30P   |
| standard                 | UL Listed, CSA Listed   |