

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301420045](#)  
**Status:** **Active**  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Description:** Super-Safeway Connector with Locking Blade, 3 Pole/4 Wire, NEMA L16-30, 3ø 480V

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA      LR6837  
 UL      E10176

**General**

Product Family      Wiring Devices  
 Series      [130142](#)  
 IP Rating      N/A  
 NEMA Configuration      NEMA L16-30  
 Overview      [Heavy-Duty Industrial Wiring Devices](#)  
 Product Literature Order No      987650-8068  
 Product Name      Super-Safeway  
 Receptacle Type      Single  
 Specialty      N/A  
 Type      Connector  
 UPC      78678870534  
 Woodhead      Yes

**Physical**

Flange      No  
 Flip Lid      No  
 Gender      Female  
 Length      N/A  
 Locking Blade      Yes  
 Poles      3-pole/4-wire

**Electrical**

Cord Type      N/A  
 Current - Maximum per Contact      30.0A  
 GFCI      No  
 Lighted Connector      No  
 Voltage - Maximum      3ø 480V

**Material Info**

Engineering Number      2976



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**China RoHS**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

**Search Parts in this Series**

[130142 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [\*\*1301420045\*\*](#)  
**Status:** **Active**  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Description:** Super-Safeway Connector with Locking Blade, 3 Pole/4 Wire, NEMA L16-30, 3Ø 480V

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA    LR6837  
 UL    E10176

**General**

Product Family    Wiring Devices  
 Series    [130142](#)  
 IP Rating    N/A  
 NEMA Configuration                                  NEMA L16-30  
 Overview    [Heavy-Duty Industrial Wiring Devices](#)  
 Product Literature Order No                          987650-8068  
 Product Name    Super-Safeway  
 Receptacle Type    Single  
 Specialty    N/A  
 Type    Connector  
 UPC    78678870534  
 Woodhead    Yes

**Physical**

Flange    No  
 Flip Lid    No  
 Gender    Female  
 Length    N/A  
 Locking Blade    Yes  
 Poles    3-pole/4-wire

**Electrical**

Cord Type    N/A  
 Current - Maximum per Contact                          30.0A  
 GFCI    No  
 Lighted Connector    No  
 Voltage - Maximum    3Ø 480V

**Material Info**

Engineering Number    2976



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**China RoHS**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130142 Series](#)