

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301470108](#)  
**Status:** **Active**  
**Overview:** [Watertite Wet-Location Wiring Solutions](#)  
**Description:** Watertite Connector with Locking Blade, 3 Pole/4 Wire, NEMA L16-30, 3ø 480V, Cord Grip Body Size F4

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA                      LR6837  
 UL                        E10176

**General**

Product Family                      Wiring Devices  
 Series                                  [130147](#)  
 Exclude SD Check                    Yes  
 IP Rating                                IP67  
 NEMA Configuration                NEMA L16-30  
 Overview                                [Watertite Wet-Location Wiring Solutions](#)  
 Product Literature Order No        987650-8067  
 Product Name                         Watertite  
 Receptacle Type                      Single  
 Specialty                                N/A  
 Type                                      Connector  
 UPC                                      78678871334

**Physical**

Cord Grip Body Size                F4 1"  
 Flange                                  No  
 Flip Lid                                 No  
 Gender                                 Female  
 Length                                 N/A  
 Locking Blade                        Yes  
 Net Weight                            441.798/g  
 Poles                                    3-pole/4-wire

**Electrical**

Cord Type                              N/A  
 Current - Maximum per Contact    30.0A  
 GFCI                                    No  
 Lighted Connector                    No  
 Voltage - Maximum                 3ø 480V

**Material Info**

Engineering Number                29W76



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130147 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301470108](#)  
**Status:** **Active**  
**Overview:** [Watertite Wet-Location Wiring Solutions](#)  
**Description:** Watertite Connector with Locking Blade, 3 Pole/4 Wire, NEMA L16-30, 3ø 480V, Cord Grip Body Size F4

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA                      LR6837  
 UL                      E10176

**General**

Product Family                      Wiring Devices  
 Series                      [130147](#)  
 Exclude SD Check                      Yes  
 IP Rating                      IP67  
 NEMA Configuration                      NEMA L16-30  
 Overview                      [Watertite Wet-Location Wiring Solutions](#)  
 Product Literature Order No                      987650-8067  
 Product Name                      Watertite  
 Receptacle Type                      Single  
 Specialty                      N/A  
 Type                      Connector  
 UPC                      78678871334

**Physical**

Cord Grip Body Size                      F4 1"  
 Flange                      No  
 Flip Lid                      No  
 Gender                      Female  
 Length                      N/A  
 Locking Blade                      Yes  
 Net Weight                      441.798/g  
 Poles                      3-pole/4-wire

**Electrical**

Cord Type                      N/A  
 Current - Maximum per Contact                      30.0A  
 GFCI                      No  
 Lighted Connector                      No  
 Voltage - Maximum                      3ø 480V

**Material Info**

Engineering Number                      29W76



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130147](#) Series