



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 2LEDDRIVERG210LM 2" 120V Driver

*Lithonia Lighting*

Catalog Number	2LEDDRIVERG210LM
Manufacturer	Lithonia Lighting
Description	Juno 2-Inch Aperture Recessed Downlight Is Ic Rated For Insulated or Non-Insulated Applications. The Sophisticated Aesthetics and Smaller Aperture Offers The "Designer-Look" That Perfectly Complements Many Of Today'S Upscale Residential and Commercial Interiors. Designed to Be Paired With A Juno 2 In. Driver Housing.
Weight per unit	1.3 (lbs/each)
Product Category	20170508170440

### Features

average life	50,000
Lamp Type	LED - Static
lumens	1000
Material	Steel
Maximum Operating Temperature	25
media	Yes
Number of Lamps	1
Voltage Rating	120
Wattage	11.5

### Material, Color, and Finish

Color	Unfinished
-------	------------

### Dimensions and Weight

Height	3
Length	12
Width	3

### Descriptions

Construction	New Construction,Remodel
Description	2" 120V DRIVER
extra long description	LITH 2LEDDRIVER G2 10LM 120 FRPC Ju
Long Description	Juno 2-inch aperture recessed downlight is IC rated for insulated or non-insulated applications. The sophisticated aesthetics and smaller aperture offers the "designer-look" that perfectly complements many of today's upscale residential and commercial interiors. Designed to be paired with a Juno 2 in. driver housing.
Product Type	Housing



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	JUNO
GTIN	00661209585127
Manufacturers Part Number	2LEDDRIVER G2 10LM 120 FRPC
UPC	661209585127

## Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
----------------------	--------------------------

## Trade Size

aperture size	2 IN
---------------	------

## Packaging

Carton	1
Weight	1.2
Weight Per each	1.31

## Uses, Certifications, and Standards

Application	Education, Government, Healthcare, Hospitality, House of Worship, Offices & Banks, Residential, Retail
environmental conditions	Indoor
Mounting	Recessed