



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 30241012 Encl 30X24X10 N12 CH Clamp CVR

*Cooper B-Line/Cable Tray*

Catalog Number	30241012
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 30" Height, 10" Length, 24" Width, Nema 12, Hinged Cover, 12 Enclosure, Wall Mount, Medium Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	58.4 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

### Features

dimensions	10.0000 IN X 24.0000 IN X 30.0000 IN
Mounting Type	Wall

### Material, Color, and Finish

Color	Gray
-------	------

### Dimensions and Weight

Size	24.00 In Width X 10.00 In Depth X 30.00 In Height
------	---

### Descriptions

Description	ENCL 30X24X10 N12 CH CLAMP CVR
extra long description	B-LINE 302410-12 TYPE 12 SGL-DOOR E
Features	Eaton's B-Line series JIC wall mount, ground mount and terminal Type 12 panel enclosures are used to house electrical controls and instruments while helping protect them against circulating dust, falling dirt and dripping non-corrosive liquids.
Long Description	Eaton B-Line series wall mounted panel enclosure, 30" height, 10" length, 24" width, NEMA 12, Hinged cover, 12 enclosure, Wall mount, Medium single door, External mounting feet, Carbon steel, Seamless poured in-place gasket
Product Type	Type 12 SGL-Door Enc, 30X24X10
Special Features	Plated door clamps

### Manufacturer Information

Brand	Eaton
GTIN	00782051803402
Manufacturers Part Number	302410-12
UPC	782051803402

### Taxonomies, Classifications, and Categories

Type	Type 12 panel enclosures
------	--------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	58.4

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Building Automation and Monitoring Datacenters - IT Space: CI and Hyper Converged Utility - Substations, Utility Transmission and Distribution Generation - Renewable Energy - Alternative Energy Commercial / Institutional Buildings / Structures - Lighting and Lighting Controls Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other Commercial / Institutional Buildings / Structures - Safety and Security System
Mounting standard	EXTERNAL FEET, WALL UL 508A, CSA C22.2., NEMA