

HOLE SAWS

MASTER-GRIT™ HOLE SAWS

Best for Cutting Abrasive Materials



Specifications (1 per box)

Product Number	Diameter (Inches)	Pipe Tap (Inches)	Pipe Entrance (Inches)	Use Arbor Number
29912-12CG	3/4	1/2	3/8	1L or 4L
29998-20MMCG	25/32			1L or 4L
29914-14CG	7/8	3/4	1/2	1L or 4L
29916-16CG	1			1L or 4L
29918-18CG	1-1/8	1	3/4	1L or 4L
29920-20CG	1-1/4			2L
29922-22CG	1-3/8		1	2L
29924-24CG	1-1/2	1-1/4		2L or 7L
29928-28CG	1-3/4	1-1/2	1-1/4	2L or 7L
29932-32CG	2		1-1/2	2L or 7L
29934-34CG	2-1/8			2L or 7L
29936-36CG	2-1/4	2		2L or 7L
29938-38CG	2-3/8			2L or 7L
29940-40CG	2-1/2		2	2L or 7L
29941-41CG	2-9/16			2L or 7L
29942-42CG	2-5/8	2-1/2		2L or 7L
29948-48CG	3		2-1/2	2L or 7L
29952-52CG	3-1/4	3		2L or 7L
29958-58CG	3-5/8		3	2L or 7L
29964-64CG	4			2L or 7L
29966-66CG	4-1/8		3-1/2	2L or 7L
30297-123CT	Carbide Tipped Pilot Drill			1 per pack
30298-65CTPD	Carbide Tipped Pilot Drill			1 per pack

THE LENOX® ADVANTAGE™

- **Cuts abrasive materials**
Super hard tungsten carbide grit cuts through fiberglass, ceramic tile, laminates and other abrasive materials.
- **Clean cutting**
Carbide grit edge will not snag or chip when cutting thin materials.

MASTER-GRIT™ RECESSED LIGHTING HOLE SAWS

Specifications (1 per box)

Product Number	Diameter (Inches)	For Fixtures
30861-438RL	4-3/8	Capri, Marco & Halo, Mini-Juno
30862-638RL	6-3/8	Capri, Halo, Pathway & Thomas
30863-658RL	6-5/8	Juno, Progress & Pathway
30864-678RL	6-7/8	Capri, Hubbell, Lightolier®, Lithonia®, Marco, Prescolite®, Progress

Use 123CT or 4321 Pilot Drill for Recessed Lighting Hole Saws.



HOLE SAWS

MASTER-GRIT™ HOLE SAWS

Best for Cutting Abrasive Materials



Specifications (1 per box)

Product Number	Diameter (Inches)	Pipe Tap (Inches)	Pipe Entrance (Inches)	Use Arbor Number
29912-12CG	3/4	1/2	3/8	1L or 4L
29998-20MMCG	25/32			1L or 4L
29914-14CG	7/8	3/4	1/2	1L or 4L
29916-16CG	1			1L or 4L
29918-18CG	1-1/8	1	3/4	1L or 4L
29920-20CG	1-1/4			2L
29922-22CG	1-3/8		1	2L
29924-24CG	1-1/2	1-1/4		2L or 7L
29928-28CG	1-3/4	1-1/2	1-1/4	2L or 7L
29932-32CG	2		1-1/2	2L or 7L
29934-34CG	2-1/8			2L or 7L
29936-36CG	2-1/4	2		2L or 7L
29938-38CG	2-3/8			2L or 7L
29940-40CG	2-1/2		2	2L or 7L
29941-41CG	2-9/16			2L or 7L
29942-42CG	2-5/8	2-1/2		2L or 7L
29948-48CG	3		2-1/2	2L or 7L
29952-52CG	3-1/4	3		2L or 7L
29958-58CG	3-5/8		3	2L or 7L
29964-64CG	4			2L or 7L
29966-66CG	4-1/8		3-1/2	2L or 7L
30297-123CT	Carbide Tipped Pilot Drill			1 per pack
30298-65CTPD	Carbide Tipped Pilot Drill			1 per pack

THE LENOX® ADVANTAGE™

- **Cuts abrasive materials**
Super hard tungsten carbide grit cuts through fiberglass, ceramic tile, laminates and other abrasive materials.
- **Clean cutting**
Carbide grit edge will not snag or chip when cutting thin materials.

MASTER-GRIT™ RECESSED LIGHTING HOLE SAWS

Specifications (1 per box)

Product Number	Diameter (Inches)	For Fixtures
30861-438RL	4-3/8	Capri, Marco & Halo, Mini-Juno
30862-638RL	6-3/8	Capri, Halo, Pathway & Thomas
30863-658RL	6-5/8	Juno, Progress & Pathway
30864-678RL	6-7/8	Capri, Hubbell, Lightolier®, Lithonia®, Marco, Prescolite®, Progress

Use 123CT or 4321 Pilot Drill for Recessed Lighting Hole Saws.

