



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 359151 Slotted 1/4" X 6" Insulated Screwdriver

*Ideal*

Catalog Number	359151
Manufacturer	Ideal
Description	Ideal, Screwdriver, Insulated, Tip Size: 1/4 In, Overall Length: 10 In, Tip Type: Slotted, Handle Length: 4.33 In, Handle Color: Black, Blade Material: 50BV30 Steel With Orange P.P. Sheathed (Dual)
Weight per unit	0.3000 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

### Features

Handle Length	4.33
Tip Size	1/4
tip type	Slotted

### Material, Color, and Finish

Blade Material	50Bv30 Steel with orange P.P. sheathed (dual)
Handle Color	Black

### Dimensions and Weight

Overall Length	10
----------------	----

### Descriptions

Description	SLOTTED 1/4" X 6" INSULATED SCREWDRIVER
extra long description	IDEAL 35-9151 INSUL SCRWDVR SLOTTD
Features	IDEAL Insulated Screwdrivers are VDE certified to 1000V AC. Each one is designed to meet ASTM F1505-01, EN, DIN and IEC 60 900 test standards. Tempered blades are finished with black oxide and super hardened for maximum quality Precision ground tips provide secure fit for less spin-out Meets OSHA requirements for insulated tools (29 CFR 1910)
Long Description	IDEAL, Screwdriver, Insulated, Tip Size: 1/4 IN, Overall Length: 10 IN, Tip Type: Slotted, Handle Length: 4.33 IN, Handle Color: Black, Blade Material: 50Bv30 Steel with orange P.P. sheathed (dual)
Product Type	Insul SCRWDVR Slotted 1 4X6

### Manufacturer Information

Brand	Ideal
GTIN	00783250731237
Manufacturers Part Number	35-9151
UPC	783250731237

### Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	INSULATED



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.3