

No. 7 Corrosive chemical pipe thread sealant

| Code | Description | Qty. |
|-------|-------------|------|
| 17432 | 1 pt. | 4 |

- FEATURES**
- Soft Set
 - Lead free

Application • Slow drying sealant for use with lines carrying corrosive chemicals: diluted acids, caustics and other chemical solutions



- Recommended for**
- Galvanized Steel
 - Iron • Brass • Copper • Aluminum
 - Stainless Steel



No. 21 Black, slow dry/soft set pipe thread sealant

| Code | Description | Qty. |
|-------|-------------|------|
| 28651 | ½ pt. | 24 |
| 28541 | 1 pt. | 12 |
| 28371 | 1 gal. | 4 |
| 28111 | 5 gal. | 1 |
| 28222 | 55 gal. | 1 |



- FEATURES**
- Black sealant
 - Lead free
 - Multi-purpose



Application • Soft set sealant for lines carrying a wide range of liquids and gases • For applications where black color is preferred

- Brushable from 20°F to 140°F

- Recommended for**
- Galvanized Steel • Iron
 - Brass • Copper • Aluminum
 - Stainless Steel
 - Polyethylene
 - RTRP • PVC

Also available in 55 gal. container.

PTFE Tape 100% pure PTFE pipe thread sealant tape

| Code | Description | Qty. |
|-------|-------------|------|
| 35942 | ½" x 260" | 12 |
| 35943 | ½" x 520" | 12 |
| 35944 | ½" x 1296" | 12 |
| 35945 | ¾" x 260" | 12 |
| 35946 | ¾" x 520" | 12 |
| 35947 | ¾" x 1296" | 12 |
| 35948 | 1" x 260" | 12 |
| 35949 | 1" x 520" | 12 |



Application • Resistant to most liquids and gases as it is completely inert

- Available in a wide variety of sizes.



No. 7 Corrosive chemical pipe thread sealant

| Code | Description | Qty. |
|-------|-------------|------|
| 17432 | 1 pt. | 4 |

- FEATURES**
- Soft Set
 - Lead free

Application • Slow drying sealant for use with lines carrying corrosive chemicals: diluted acids, caustics and other chemical solutions



- Recommended for**
- Galvanized Steel
 - Iron • Brass • Copper • Aluminum
 - Stainless Steel



No. 21 Black, slow dry/soft set pipe thread sealant

| Code | Description | Qty. |
|-------|-------------|------|
| 28651 | ½ pt. | 24 |
| 28541 | 1 pt. | 12 |
| 28371 | 1 gal. | 4 |
| 28111 | 5 gal. | 1 |
| 28222 | 55 gal. | 1 |



- FEATURES**
- Black sealant
 - Lead free
 - Multi-purpose



Application • Soft set sealant for lines carrying a wide range of liquids and gases • For applications where black color is preferred • Brushable from 20°F to 140°F

- Recommended for**
- Galvanized Steel • Iron
 - Brass • Copper • Aluminum
 - Stainless Steel
 - Polyethylene
 - RTRP • PVC

Also available in 55 gal. container.

PTFE Tape 100% pure PTFE pipe thread sealant tape

| Code | Description | Qty. |
|-------|-------------|------|
| 35942 | ½" x 260" | 12 |
| 35943 | ½" x 520" | 12 |
| 35944 | ½" x 1296" | 12 |
| 35945 | ¾" x 260" | 12 |
| 35946 | ¾" x 520" | 12 |
| 35947 | ¾" x 1296" | 12 |
| 35948 | 1" x 260" | 12 |
| 35949 | 1" x 520" | 12 |



Application • Resistant to most liquids and gases as it is completely inert

- Available in a wide variety of sizes.

