



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



35976 HD Ship Auger 7/8 In

Ideal

| | |
|------------------|--|
| Catalog Number | 35976 |
| Manufacturer | Ideal |
| Description | Ideal, Auger Bit, Resi-Master, Long Ship, Heavy-Duty, Bit Diameter: 7/8 In, Shank Diameter: 7/16 In, Twist Length: 15 In, Overall Length: 18 In, Flute Type: Single-Helix, Cutting Edge Angle: 62 Deg |
| Weight per unit | 1.3 (lbs/each) |
| Product Category | Bits, Parts, Accessories |

Features

| | |
|----------------|--------------|
| Flute Type | Single-Helix |
| Shank Diameter | 7/16 |
| Twist Length | 15 |

Dimensions and Weight

| | |
|----------------|----|
| Overall Length | 18 |
|----------------|----|

Descriptions

| | |
|------------------------|---|
| Description | HD SHIP AUGER 7/8 IN |
| extra long description | IDEAL 35-976 Auger Bit,Ideal,RESI-M |
| Features | 62° cutting angle reinforces the cutting edge and provides greater durabilityHardened lead screw and cutting edge provide increased wear resistance and extended lifeSecondary relief angle evacuates wood chips quickly and prevents auger from jammingOversized cutting head makes hole larger than body of bit for easy ejection from work piece |
| Long Description | IDEAL, Auger Bit, RESI-MASTER, Long Ship, Heavy-Duty, Bit Diameter: 7/8 IN, Shank Diameter: 7/16 IN, Twist Length: 15 IN, Overall Length: 18 IN, Flute Type: Single-Helix, Cutting Edge Angle: 62 DEG |
| Product Type | Auger Bit, Ideal, Resi-Master, LG Ship, Heavy-Duty, 7/8 In Bit Di |
| Special Features | Features: 62 DEG Reinforced Cutting Edge For Added Durability; Precision Ground, Self-Feeding Lead Screw; Secondary Relief Angle For Efficient Chip Removal; Hardened Lead Screw And Cutting Edge Powers Through Nails And Staples And Extends Tool Life; Hardened And Tempered Shaft Minimizes Warping; Quick-Change Shank Design For Fast Bit Changes And Use With Pneumatic Drills; 7/8 IN Hole Diameter; Overall Length Of 18 IN; Twist Length Of 15 IN; Oversized Cutting Head Makes Hole Larger Than Body Of Bit For Easy |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250632961 |
| Manufacturers Part Number | 35-976 |
| UPC | 783250632961 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------|
| Category Description | TOOL BAG/POUCHES |
| Type | Long Ship, Heavy-Duty |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 1.3 |

Uses, Certifications, and Standards

| | |
|----------|------|
| standard | RoHS |
|----------|------|