



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



36361212 Encl 36X36X12 N12 1DR CH Clamp CVR *Cooper B-Line/Cable Tray*

Catalog Number	36361212
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 36" Height, 12" Length, 36" Width, Nema 12, Hinged Cover, 12 Enclosure, Wall Mount, Medium Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	97.5 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Features

dimensions	12.0000 IN X 36.0000 IN X 36.0000 IN
Mounting Type	Wall

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Size	36.00 In Width X 12.00 In Depth X 36.00 In Height
------	---

Descriptions

Description	ENCL 36X36X12 N12 1DR CH CLAMP CVR
extra long description	B-LINE 363612-12 TYPE 12 SGL-DOOR E
Features	Eaton's B-Line series JIC wall mount, ground mount and terminal Type 12 panel enclosures are used to house electrical controls and instruments while helping protect them against circulating dust, falling dirt and dripping non-corrosive liquids.
Long Description	Eaton B-Line series wall mounted panel enclosure, 36" height, 12" length, 36" width, NEMA 12, Hinged cover, 12 enclosure, Wall mount, Medium single door, External mounting feet, Carbon steel, Seamless poured in-place gasket
Product Type	Type 12 SGL-Door Enc, 36X36X12
Special Features	Plated door clamps

Manufacturer Information

Brand	Eaton
GTIN	00782051408348
Manufacturers Part Number	363612-12
UPC	782051408348

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Type 12 panel enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	97.499

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Building Automation and Monitoring Commercial / Institutional Buildings / Structures - Commercial/Inst Bldg Structures - Aftermarket Generation - Renewable Energy - Alternative Energy Utility - Substations, Utility Transmission and Distribution Commercial / Institutional Buildings / Structures - Power Distribution and Controls Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other Datacenters - IT Space: CI
Mounting standard	EXTERNAL FEET, WALL CSA C22.2, UL 508A, NEMA