



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



389 3-1/2" Mall GRND Bushing *Bridgeport Fittings*

| | |
|------------------|--|
| Catalog Number | 389 |
| Manufacturer | Bridgeport Fittings |
| Description | Bushing, Insulated, Grounding, Malleable Iron, Size 3-1/2 Inch, 14-1/0 Lug |
| Weight per unit | 0.7200 (lbs/each) |
| Product Category | Rigid Conduit Fittings - Steel |

Features

| | |
|----------|----------------|
| Material | Malleable Iron |
| media | Yes |

Material, Color, and Finish

| | |
|--------|---------------------------|
| Color | Grey with Black Insulator |
| Finish | Zinc Electroplated |

Dimensions and Weight

| | |
|------|-------|
| Size | 3-1/2 |
|------|-------|

Descriptions

| | |
|------------------------|--|
| Description | 3-1/2" MALL GRND BUSHING |
| extra long description | BPT 389 3-1/2"Grd.Bush.Ins.14-1/0 M |
| Long Description | Bushing, Insulated, Grounding, Malleable Iron, Size 3-1/2 Inch, 14-1/0 Lug |
| Product Type | 3-1/2"GRD.Bush.Ins.14-1/0 Mall |
| Special Features | Grounding Lug Wire Capacity #14 - #1/0 |

Manufacturer Information

| | |
|-------|---------------------|
| Brand | Bridgeport Fittings |
| GTIN | 00781747003898 |
| UPC | 781747003898 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | COUPLINGS, ADAPTERS, REDUCERS, BUSHINGS, & CAPS |
| Type | BUSHING |

Trade Size

| | |
|------------|-----|
| Trade Size | 3.5 |
|------------|-----|

Packaging

| | |
|-----------------|------|
| Carton | 25 |
| Weight Per each | 0.72 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------|---|
| Application | Used with locknut to terminate service conduit to cabinet. Lug provided for bonding jumper to neutral busbar. |
| standard | cULus |
| Temperature Rating | 150°C |