

Eaton 3BR4242B400R

Catalog Number: 3BR4242B400R

Eaton BR main breaker loadcenter, Main circuit breaker, 400 A, Aluminum, NEMA 3R, 42 Circuits, 42 Spaces, Three-phase, Surface, NEMA 3R, Factory integrated surge, No feed thru lugs



Photo is representative

General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	3BR4242B400R
UPC	Product Length/Depth
786685895321	89 in
Product Height	Product Width
6 in	19 in
Product Weight	Warranty
96 lb	10 year limited

Certifications

UL 67
UL Listed file E52977

defaultTaxonomyAttributeLabel

Type

Main circuit breaker

Amperage Rating

400 A

Bus material

Aluminum

Number of circuits

42

Number of spaces

42

Phase

Three-phase

Mounting

Surface

Options

Factory integrated surge, No feed thru lugs

Enclosure

NEMA 3R

Interrupt rating

22 kAIC

NEMA rating

NEMA 3R

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

[Type BR 3-Phase Loadcenters](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - 3BR4242B400R](#)

[3-Phase Loadcenter Program](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton 3BR4242B400R

Catalog Number: 3BR4242B400R

Eaton BR main breaker loadcenter, Main circuit breaker, 400 A, Aluminum, NEMA 3R, 42 Circuits, 42 Spaces, Three-phase, Surface, NEMA 3R, Factory integrated surge, No feed thru lugs



Photo is representative

General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	3BR4242B400R
UPC	Product Length/Depth
786685895321	89 in
Product Height	Product Width
6 in	19 in
Product Weight	Warranty
96 lb	10 year limited

Certifications

UL 67
UL Listed file E52977

defaultTaxonomyAttributeLabel

Type

Main circuit breaker

Amperage Rating

400 A

Bus material

Aluminum

Number of circuits

42

Number of spaces

42

Phase

Three-phase

Mounting

Surface

Options

Factory integrated surge, No feed thru lugs

Enclosure

NEMA 3R

Interrupt rating

22 kAIC

NEMA rating

NEMA 3R

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

[Type BR 3-Phase Loadcenters](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - 3BR4242B400R](#)

[3-Phase Loadcenter Program](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia