

Eaton 3MM420RRL

Catalog Number: 3MM420RRL

Eaton's Three-Phase Residential Meter Stack Module, Group Metering Type, 200A, Aluminum Bus 800 Ampere, No bypass, Outdoor, Five-jaws, 4 Sockets, Three-phase in, single-phase out, Ringless Security, 120/208V



General specifications

| | |
|-------------------------------|--|
| Product Name | Catalog Number |
| Eaton residential meter stack | 3MM420RRL |
| UPC | Product Length/Depth |
| 786849052201 | 62.5 in |
| Product Height | Product Width |
| 8.3 in | 16.3 in |
| Product Weight | Warranty |
| 77.2 lb | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| Certifications | |
| UL Listed | |

defaultTaxonomyAttributeLabel

Type

Group Metering

Utility approvals

ME : Central Maine Power

NC : Dominion

VA : Dominion

ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company)

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

GA : Georgia Power

KS : Kansas City Power and Light (KCPL) / Westar Energy

MO : Kansas City Power and Light (KCPL) / Westar Energy

TN : Middle Tennessee EMC

NM : Public Service Company of New Mexico (PNM)

FL : Tallahassee City Electric

SC : South Carolina Electric and Gas (SCE&G)

IN : Indiana Michigan Power (IMP) (AEP East)

MI : Indiana Michigan Power (IMP) (AEP East)

OH : AEP Ohio (AEP East)

TN : Appalachian Power (AEP East)

VA : Appalachian Power (AEP East)

WV : Appalachian Power (AEP East)

TX : Texas-New Mexico Power (TNMP)

NM : Texas-New Mexico Power (TNMP)

Interrupt rating

Depends on selected main circuit breaker

Enclosure

Outdoor

Secondary circuit breaker

CCV2_X, CCVH2_X, CVS2_XMM, CV2_XMM, CVH2_XMM

Bus Rating

800 A

Phase

Three-phase in, single-phase out

Voltage rating

120/208V

Amperage Rating

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - METER MODULES, DIMENSIONS, 200A, MM, TMP

Specifications and datasheets

Eaton Specification Sheet - 3MM420RRL

200A

Bus material

Aluminum

Bypass

None

Number of jaws

Five-jaw

Number of sockets

4

Phase balance

A-B

Security

Ringless



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia