



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 4250L4 250 Al/Cu 4 Barrel Lug

*Nsi Industries*

|                  |   |
|------------------|---|
| Catalog Number   | 4250L4  |
| Manufacturer     | Nsi Industries  |
| Description      | 4 Port Panelboard Lug 250 MCM - 6 Awg Large Size Set Screw Connectors With Multiple Mounting Holes For A Secure, Turn-Prevent Connection. Made Of 6061T-6 Aluminum Alloy. Tin Plated For Low Contact Resistance. For Use With Copper or Aluminum Conductors. 600V (2000V Max, Per UL486B). UL 486A/B Listed. Temperature Rating 90 Degrees C. All Hole Spacing Is Nema Standard Of 1.75". |
| Weight per unit  | 0.6700 (lbs/each)   |
| Product Category | Large Terminals & Connectors  |

### Features

|                |        |
|----------------|--------|
| Voltage Rating | 600 V  |
| Warranty       | 1 YEAR |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 250 AL/CU 4 BARREL LUG  |
| extra long description | NSI 4-250L4 AL/CU CONN. 4-14 AWG 11   |
| Features               | 4 Port Panelboard Lug 250 MCM - 6 AWG Large size set screw connectors with multiple mounting holes for a secure, turn-prevent connection. Made of 6061T-6 aluminum alloy. Tin plated for low contact resistance. For use with copper or aluminum conductors. 600V (2000V max, per UL486B). UL 486A/B Listed. Temperature rating 90 degrees C. All hole spacing is NEMA standard of 1.75". |
| Long Description       | 4 Port Panelboard Lug 250 MCM - 6 AWG Large size set screw connectors with multiple mounting holes for a secure, turn-prevent connection. Made of 6061T-6 aluminum alloy. Tin plated for low contact resistance. For use with copper or aluminum conductors. 600V (2000V max, per UL486B). UL 486A/B Listed. Temperature rating 90 degrees C. All hole spacing is NEMA standard of 1.75". |
| Product Type           | Al/Cu Conn. 4-14 Awg 11 Holes 9 Circuits  |
| Special Features       | (4) 250 MCM-6 AWG - Dual Rated - Pack   |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | NSi            |
| GTIN                      | 00662381001603 |
| Manufacturers Part Number | 4-250L4        |
| UPC                       | 662381001603   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... SPLIT BOLTS

Type ..... Panelboard Lug

## Packaging

Carton ..... 1

Package ..... 2

Weight Per each ..... 0.67

## Uses, Certifications, and Standards

Application ..... Wire Termination

standard ..... cULus