



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



430LT12 1/2" Ins Sealtight Straight Diecast Connector *Bridgeport Fittings*

| | |
|------------------|---|
| Catalog Number | 430LT12 |
| Manufacturer | Bridgeport Fittings |
| Description | Connector, Liquid Tight, Zinc Die Cast, Insulated Throat, Size 1/2 Inch |
| Weight per unit | 0.1461 (lbs/each) |
| Product Category | Liquid Tight Fittings |

Features

| | |
|----------------|---------------------|
| angle | Straight |
| Connector Type | Straight, Insulated |
| Material | Zinc Die Cast |
| media | Yes |

Material, Color, and Finish

| | |
|--------|--------------|
| Finish | Ball burnish |
|--------|--------------|

Dimensions and Weight

| | |
|------|-----|
| Size | 1/2 |
|------|-----|

Descriptions

| | |
|------------------------|---|
| Description | 1/2" INS SEALTIGHT STRAIGHT DIECAST CONNECTOR |
| extra long description | BPT 430-LT12 1/2" LQDT CONN. INS. |
| Long Description | Connector, Liquid Tight, Zinc Die Cast, Insulated Throat, Size 1/2 Inch |
| Product Type | 1/2" LQDT Conn. Ins. |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Bridgeport |
| GTIN | 00781747164308 |
| Manufacturers Part Number | 430-LT12 |
| UPC | 781747164308 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------|
| Category Description | METALLIC FITTINGS |
| Type | CONNECTOR |

Trade Size

| | |
|------------|-----|
| Trade Size | 1/2 |
|------------|-----|

Packaging

| | |
|-----------------|--------|
| Carton | 25 |
| Package | 100 |
| Weight Per each | 0.1461 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Straight connector for use with metallic and non-metallic "Type B" liquid tight conduit. Insulator rated 105 degree C.

standard

UL, CSA