



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



4125ST 1-1/4 In Emt SSCR Conn Insul Steel *Appleton/Oz Gedney*

| | |
|------------------|--|
| Catalog Number | 4125ST |
| Manufacturer | Appleton/Oz Gedney |
| Description | Features:1 3/4IN Dia X 1 11/16IN Length, 9/16 In Thread Length, Concretetight, Standard:UI 514B, Csa C22.2, Nema FB-1, Size:1.25IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated, Insulation:Insulated Throat, Temperature Rating:90ce |
| Weight per unit | 0.4000 (lbs/each) |
| Product Category | Steel Insulated Straight Set S |

Features

| | |
|----------------|------------------|
| connection | Male NPS Thread |
| Connector Type | SET SCREW |
| insulation | Insulated Throat |
| Material | Steel |

Material, Color, and Finish

| | |
|--------|---------------------|
| Color | Metallic |
| Finish | Zinc Electro Plated |

Dimensions and Weight

| | |
|------|------|
| Size | 1.25 |
|------|------|

Descriptions

| | |
|------------------------|---|
| Description | 1-1/4 IN EMT SSCR CONN INSUL STEEL |
| extra long description | EGS 4125ST 1-1/4 IN EMT SSCR CONN I |
| Long Description | Features:1 3/4IN Dia X 1 11/16IN Length, 9/16 IN Thread Length, Concretetight, Standard:UL 514B, CSA C22.2, NEMA FB-1, Size:1.25IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated,Insulation:Insulated Throat, Temperature Rating:90CE |
| Product Type | 1-1/4 In Emt SSCR Conn Insul Steel |
| Special Features | 1-1/4 IN Trade Size Connector for EMT Conduit, Set Screw Type, Male Hub Threads NPS, Body Length 1.75 IN, Max. Dia. 1.69 IN,Thread Length 0.56 IN, Concretetight when taped, Male Hub Threads - NPS, Insulated Throat |

Manufacturer Information

| | |
|---------------------------|--------------------|
| Brand | Appleton/Oz Gedney |
| GTIN | 00687855846184 |
| Manufacturers Part Number | 4125ST |
| UPC | 687855846184 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Type EMT Conduit Straight Set Screw Connector

Trade Size

Trade Size 1.25

Packaging

Carton 1

Weight Per each 0.4

Uses, Certifications, and Standards

Application To ground and secure EMT Raceways to boxes and enclosures

nema rating FB-1

standard UL Standard: 514B; UL Listed: E14815, E14895; CSA Standard:
C22.2 No. 18.3, cUL Listed: E14895, CSA Certified: 028507;
NEMA: FB-1

Temperature Rating 90