



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **414110ST Zinc Die-Cast, 1/2" Knockout MC Cable Connector SN** *Arlington Industries*

Catalog Number	414110ST
Manufacturer	Arlington Industries
Description	Zinc Die-Cast, 1/2" Knockout MC Cable Connector Snaps Quickly On to The Conduit With A Removable Screw In Spring Steel Clip and Then Snaps Into Knockout With External Spring Steel Clip, No Tools Required. Concrete Tight When Taped. Wider Cable Range. Supports 2 Cables.
Weight per unit	0.1640 (lbs/each)
Product Category	BX, MC, Armored Cable Fittings

### **Features**

Material	Zinc
----------	------

### **Material, Color, and Finish**

Color	Silver
Finish	Silver

### **Dimensions and Weight**

Size	L(2.500) x W(2.386) x H(0.950)
------	--------------------------------

### **Descriptions**

Construction	Die-Cast
Description	ZINC DIE-CAST, 1/2" KNOCKOUT MC CABLE CONNECTOR SN
extra long description	ARL 414110ST SNAP2IT SNAP IN DUPLEX
Long Description	Zinc die-cast, 1/2" Knockout MC cable connector snaps quickly on to the conduit with a removable screw in spring steel clip and then snaps into knockout with external spring steel clip, no tools required. Concrete tight when taped. Wider Cable Range. Supports 2 cables.
Product Type	SNAP2IT Snap In Duplex
Special Features	Duplex Connector

### **Manufacturer Information**

Brand	ARLINGTON
GTIN	00018997007292
Manufacturers Part Number	414110ST
UPC	018997007292

### **Taxonomies, Classifications, and Categories**

Category Description	FORM 7, 8, CONDULETS, COVERS, & GASKETS
Type	Snap-on

### **Trade Size**

Trade Size	3/8
------------	-----



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	25
Package	100
Weight Per each	0.164

## Uses, Certifications, and Standards

Application	AC/MC/HCF/MCI-A/AC90/ACG90/Flex/MC-PCS
standard	CULUS and CSA