



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 4250S 2-1/2" STL Set SCR Emt Conn *Appleton/Oz Gedney*

Catalog Number	4250S
Manufacturer	Appleton/Oz Gedney
Description	Features:2 5/32IN Dia X 3 7/16IN Length, 7/8 In Thread Length, Concretetight, Standard:UI 514B, Csa C22.2, Nema FB-1, Size:2.5IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated
Weight per unit	1.2 (lbs/each)
Product Category	Steel Uninsulated Straight Set

### Features

connection	Male NPS Thread
insulation	Not insulated
Material	Steel

### Material, Color, and Finish

Color	Metallic
Finish	Zinc Electro Plated

### Dimensions and Weight

Size	2.5
------	-----

### Descriptions

Description	2-1/2" STL SET SCR EMT CONN
extra long description	EGS 4250S 2-1/2 IN EMT SSCR CONN
Long Description	Features:2 5/32IN Dia X 3 7/16IN Length, 7/8 IN Thread Length, Concretetight, Standard:UL 514B, CSA C22.2, NEMA FB-1, Size:2.5IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated
Product Type	2-1/2 In Emt SSCR Conn
Special Features	2-1/2 IN Trade Size Connector for EMT Conduit, Set Screw Type, Male Hub Threads NPS, Body Length 2.38 IN, Max. Dia. 3.13 IN,Thread Length 0.88 IN, Concretetight when taped, Male Hub Threads - NPS

### Manufacturer Information

Brand	Appleton
GTIN	00687855846313
Manufacturers Part Number	4250S
UPC	687855846313

### Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	EMT Conduit Straight Set Screw Connector



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	10
Weight Per each	1.21

## Uses, Certifications, and Standards

Application	To ground and secure EMT Raceways to boxes and enclosures
nema rating	FB-1
standard	UL Standard: 514B; UL Listed: E14815, E14895; CSA Standard: C22.2 No. 18.3, cUL Listed: E14895, CSA Certified: 028507; NEMA: FB-1