



Catalog Number: 4460-GSC3R-NK  
Item Description: N3R SCREW CVR GUTTER NK  
UPC Code: 784572106673


Brand Name: Milbank  
Type: Wiring Trough  
Special Features: Key Locking Cylinder Latch Provision,  
Sealing Eye Lance  
Application: Wireway  
Standard: UL Listed, Type 3R  
Cover Type: Screw Cover  
Enclosure: Outdoor Enclosure  
Nominal Cross Section: 4x4  
Straight Section Length: 60  
Material: Steel with Powder Coat Finish  
Finish: ANSI 61 Gray  
Knockouts: False





*Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.*

CAT. NO.	U/L LABEL
4460-GSC3R-( )	1002943
RC-4460-GSC3R-( )	1125051
SPRSCG-4460-( )	1132575

ITEM	QTY.	PART NUMBER	DESCRIPTION
1	1	(SEE CHART)	BACK WELDMENT
2	1	(SEE CHART)	FRONT
3	5	1001290	SCREW, 10-32 X 5/16
4	1	1002898	LABEL, RATING 4x4 GSC3R
5	1	(SEE CHART)	UL LABEL, WIREWAY



SUFFIX	FINISH	BACK WELDMENT	FRONT NO.	INSTALL K.O.s
NONE	MILBANK LIGHT GRAY	1153005	1164989	YES
-NP	NONE	1164871	1010772	
-NK	MILBANK LIGHT GRAY	1153016	1164989	NO
-NK-NP	NONE	1164872	1010772	

Material:	16 GA. GALV. STEEL	 <p><b>MILBANK</b> ENERGY AT WORK</p>
Shear/ Die#:		
Finish:	SEE CHART	General Offices: Kansas City, MO
Part Wt.:		Title: SCREW COVER WIREWAY NEMA TYPE 3R
Tolerances:	Third Angle	Catalog No.: (SEE CHART)
Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X* ±2*		Customer:
Scale:	NTS	Checked By:
Drawn By:	D.F.	Approved By:
Date:	5/11/11	Drawing No.: <b>1003666</b>
Sheet	1 of 1	

REV.	DATE	DESCRIPTION	BY
B3	5/11/11	REDRAW INTO SOLIDWORKS; UPDATE K.O. PATTERN; CHART -NK VERSION (ECO #20576)	D.F.
B4	5/24/13	CHART FINISH (ECO #23988)	D.F.
B5	6/6/13	CHART: 1164989 WAS 1010772, 1010772 WAS 1010761 (ECO #24050)	D.F.



Catalog Number: 4460-GSC3R-NK  
Item Description: N3R SCREW CVR GUTTER NK  
UPC Code: 784572106673


Brand Name: Milbank  
Type: Wiring Trough  
Special Features: Key Locking Cylinder Latch Provision,  
Sealing Eye Lance  
Application: Wireway  
Standard: UL Listed, Type 3R  
Cover Type: Screw Cover  
Enclosure: Outdoor Enclosure  
Nominal Cross Section: 4x4  
Straight Section Length: 60  
Material: Steel with Powder Coat Finish  
Finish: ANSI 61 Gray  
Knockouts: False





*Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.*

CAT. NO.	U/L LABEL
4460-GSC3R-( )	1002943
RC-4460-GSC3R-( )	1125051
SPRSCG-4460-( )	1132575

ITEM	QTY.	PART NUMBER	DESCRIPTION
1	1	(SEE CHART)	BACK WELDMENT
2	1	(SEE CHART)	FRONT
3	5	1001290	SCREW, 10-32 X 5/16
4	1	1002898	LABEL, RATING 4x4 GSC3R
5	1	(SEE CHART)	UL LABEL, WIREWAY



SUFFIX	FINISH	BACK WELDMENT	FRONT NO.	INSTALL K.O.s
NONE	MILBANK LIGHT GRAY	1153005	1164989	YES
-NP	NONE	1164871	1010772	
-NK	MILBANK LIGHT GRAY	1153016	1164989	NO
-NK-NP	NONE	1164872	1010772	

Material:	16 GA. GALV. STEEL	 <p><b>MILBANK</b> ENERGY AT WORK</p>
Shear/ Die#:		
Finish:	SEE CHART	General Offices: Kansas City, MO
Part Wt.:		Title: SCREW COVER WIREWAY NEMA TYPE 3R
Tolerances:	Third Angle	Catalog No.: (SEE CHART)
Unless Specified Otherwise		Customer:
X.X ±.1		Drawing No.: <b>1003666</b>
X.XX ±.03		Date: 5/11/11
X.XXX ±.015		Sheet 1 of 1
X* ±2*		
Scale:	NTS	Checked By:
Drawn By:	D.F.	Approved By:

REV.	DATE	DESCRIPTION	BY
B3	5/11/11	REDRAW INTO SOLIDWORKS; UPDATE K.O. PATTERN; CHART -NK VERSION (ECO #20576)	D.F.
B4	5/24/13	CHART FINISH (ECO #23988)	D.F.
B5	6/6/13	CHART: 1164989 WAS 1010772, 1010772 WAS 1010761 (ECO #24050)	D.F.