



## MC/AC CABLE TO METAL STUD CLIP, 14-2 TO 12-3 MC/AC

### CATALOG NUMBER

**449**



### CERTIFICATIONS



### FEATURES

Easily attaches MC or AC to metal stud

No tools required for installation

Provides fast installation

### PRODUCT ATTRIBUTES

Material: Spring Steel

Finish: nVent CADDY Armour

Outer Diameter: 0.430" - 0.53"

MC/AC Cable Size: 14-2 to 12-3

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction,

property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

**Europe**

Netherlands:

+31 800-0200135

France:

+33 800 901 793

**Europe**

Germany:

800 1890272

Other Countries:

+31 13 5835404

**APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**



## MC/AC CABLE TO METAL STUD CLIP, 14-2 TO 12-3 MC/AC

### CATALOG NUMBER

---

**449**



### CERTIFICATIONS

---



### FEATURES

---

Easily attaches MC or AC to metal stud

No tools required for installation

Provides fast installation

### PRODUCT ATTRIBUTES

---

Material: Spring Steel

Finish: nVent CADDY Armour

Outer Diameter: 0.430" - 0.53"

MC/AC Cable Size: 14-2 to 12-3

### WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction,

property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

**Europe**

Netherlands:

+31 800-0200135

France:

+33 800 901 793

**Europe**

Germany:

800 1890272

Other Countries:

+31 13 5835404

**APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**