



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



44916 Padlock, Xenoy, 1-1/2" Shackle, Red, W/Key, 1/CD

Ideal

| | |
|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | 44916 |
| Manufacturer | Ideal |
| Description | Ideal, Padlock, Lockout, Lock Material: Xenoy Body, Color: Blue, Width: 1-1/2 In, Shackle Diameter: 1/4 In, Finish: Non-Conductive, Lightweight Xenoy Body |
| Weight per unit | 0.2830 (lbs/each) |
| Product Category | Safety Equipment |

Material, Color, and Finish

| | |
|-------|------|
| Color | Blue |
|-------|------|

Dimensions and Weight

| | |
|-------|-------|
| Width | 1-1/2 |
|-------|-------|

Descriptions

| | |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | PADLOCK, XENOY, 1-1/2" SHACKLE, RED, W/KEY, 1/CD |
| extra long description | IDEAL 44-916 Padlock,Ideal,Lockout, |
| Features | IDEAL Safety Lockout Padlocks with Key Retention feature a non-conductive, lightweight body and the color-coding reduces confusion with other locks. Key retention ensures keys do not get lost while not in use and that padlocks are not left untouched. Complies with OSHA's "1-key, 1-lock". Comes in four colors for easy identification. |
| Long Description | IDEAL, Padlock, Lockout, Lock Material: Xenoy Body, Color: Blue, Width: 1-1/2 IN, Shackle Diameter: 1/4 IN, Finish: Non-conductive, lightweight Xenoy body |
| Product Type | Padlock, Ideal, Lockout, Xenoy Bdy Lock, Blu, 1-1/2 In W, PKG: CD |
| Special Features | Features: Dedicated Safety Lockout Device Reduces Confusion With Other Locks; Complies With OshaS 1-Key, 1-Lock; Non-Conductive, Lightweight Xenoy Body; Key Retention Ensures Keys Do Not Get Lost While Not In Use And That Padlocks Are Not Left Untouched; 1-1/2 In Shackle Clearance; 1-1/2 In Wide Lock With 1/4 In Shackle; Four Colors For Easy Identification; Keyed-Alike, Master-Keyed, 2Nd Key, Additional Colors And Engraving Available By Special Order; Shackle Diameter: 1/4 IN; Finish: Non-conductive, light |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250449163 |
| Manufacturers Part Number | 44-916 |
| UPC | 783250449163 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description SAFETY PRODUCTS

Type Lockout

Packaging

Carton 1

Weight Per each 0.283

Uses, Certifications, and Standards

standard RoHS