


470 Specular Reflector


-  470SC White Trim with Clear Specular Reflector
-  470H White Trim with Haze Reflector
-  470CG White Trim with Champagne Gold Reflector
-  470RG White Trim with Residential Gold Reflector




HOUSING / LAMP:
 H270ICAT: 13W DTT or 13W TTT
 H270RICAT: 13W DTT or 13W TTT
 H271ICAT: 18W DTT or 18W TTT
 H271RICAT: 18W DTT or 18W TTT
 H272ICAT: 26W DTT or 26W TTT
 H272RICAT: 26W DTT or 26W TTT
 H273ICAT1D: 26W DTT or 26W TTT, 32W TTT
 H273RICAT1D: 26W DTT or 26W TTT, 32W TTT

DIMENSIONS: Height: 6-1/4" [159mm]; OD: 7-1/8" [181mm]

70 Albalite Glass Lens


-  70P White Trim with Frosted Albalite Glass Lens
-  70PS White Trim with Frosted Albalite Glass Lens, Wet Location Listed




HOUSING / LAMP:
 H270ICAT: 13W DTT or 13W TTT
 H270RICAT: 13W DTT or 13W TTT
 H271ICAT: 18W DTT or 18W TTT
 H271RICAT: 18W DTT or 18W TTT

DIMENSIONS: OD: 8" [203mm]

271 Drop Opal Lens

-  271PS White Trim with Drop Opal Glass Lens, Wet Location Listed




HOUSING / LAMP:
 H270ICAT: 13W DTT or 13W TTT
 H270RICAT: 13W DTT or 13W TTT
 H271ICAT: 18W DTT or 18W TTT
 H271RICAT: 18W DTT or 18W TTT
 H272ICAT: 26W DTT or 26W TTT
 H272RICAT: 26W DTT or 26W TTT
 H273ICAT1D: 26W DTT or 26W TTT, 32W TTT
 H273RICAT1D: 26W DTT or 26W TTT, 32W TTT

DIMENSIONS: Height: 6-1/2" [165mm]; OD: 8" [203mm]

73 Fresnel Glass Lens


-  73P White Trim with Fresnel Glass Lens
-  73PS White Trim with Fresnel Glass Lens, Wet Location




HOUSING / LAMP:
 H270ICAT: 13W DTT or 13W TTT
 H270RICAT: 13W DTT or 13W TTT
 H271ICAT: 18W DTT or 18W TTT
 H271RICAT: 18W DTT or 18W TTT

DIMENSIONS: OD: 8" [203mm]

270 Albalite Glass Lens with Reflectors

-  270PS White Trim with Frosted Albalite Glass Lens, Wet Location Listed




HOUSING / LAMP:
 H270ICAT: 13W DTT or 13W TTT
 H270RICAT: 13W DTT or 13W TTT

H271ICAT: 18W DTT or 18W TTT
 H271RICAT: 18W DTT or 18W TTT
 H272ICAT: 26W TTT
 H272RICAT: 26W TTT
 H273ICAT1D: 26W TTT or 32W TTT
 H273RICAT1D: 26W TTT or 32W TTT

DIMENSIONS: Height: 6-5/8" [168mm]; OD: 8" [203mm]

272 Dome Lens with Reflectors

-  272PS White Trim with Frosted Glass Dome, Wet Location Listed




HOUSING / LAMP:
 H270ICAT: 13W DTT or 13W TTT
 H270RICAT: 13W DTT or 13W TTT
 H271ICAT: 18W DTT or 18W TTT
 H271RICAT: 18W DTT or 18W TTT
 H272ICAT: 26W DTT or 26W TTT
 H272RICAT: 26W DTT or 26W TTT
 H273ICAT1D: 26W DTT or 26W TTT, 32W TTT
 H273RICAT1D: 26W DTT or 26W TTT, 32W TTT

DIMENSIONS: Height: 5-1/2" [140mm]; OD: 7-3/4" [197mm]

75 Diffuser


-  75 All Glass Diffuser




HOUSING / LAMP:
 H270ICAT: 13W DTT or 13W TTT
 H270RICAT: 13W DTT or 13W TTT
 H271ICAT: 18W DTT or 18W TTT
 H271RICAT: 18W DTT or 18W TTT

DIMENSIONS: OD: 7-3/4" [197mm]

370W Regressed Albalite Glass Lens with Baffle

-  370W Regressed Albalite Glass Lens with White Baffle




HOUSING / LAMP:
 H270ICAT: 13W DTT or 13W TTT
 H270RICAT: 13W DTT or 13W TTT
 H271ICAT: 18W DTT or 18W TTT
 H271RICAT: 18W DTT or 18W TTT
 H272ICAT: 26W TTT
 H272RICAT: 26W TTT
 H273ICAT1D: 26W TTT
 H273RICAT1D: 26W TTT

DIMENSIONS: Height: 6" [152mm]; OD: 7-3/4" [197mm]

406 Baffle

-  406WWB White Baffle with White Reflector and Torsion Springs
-  406WB White Baffle with Clear Specular Reflector and Torsion Springs
-  406BA Black Baffle with Clear Specular Reflector and Torsion Springs



HOUSING / LAMP:
 H270ICAT: 13W DTT or 13W TTT
 H270RICAT: 13W DTT or 13W TTT
 H271ICAT: 18W DTT or 18W TTT
 H271RICAT: 18W DTT or 18W TTT
 H272ICAT: 26W DTT or 26W TTT
 H272RICAT: 26W DTT or 26W TTT
 H273ICAT1D: 26W DTT or 26W TTT, 32W TTT
 H273RICAT1D: 26W DTT or 26W TTT, 32W TTT


DIMENSIONS: Height: 6" [152mm]; OD: 7-3/4" [184mm]

Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Representative or visit www.cooperlighting.com for available options, accessories and ordering information.

424 Wall Wash / Reflector Downlight



424P White Trim with Specular clear reflector and wall wash reflector



HOUSING / LAMP:

H270ICAT: 13W DTT or 13W TTT
 H270RICAT: 13W DTT or 13W TTT
 H271ICAT: 18W DTT or 18W TTT
 H271RICAT: 18W DTT or 18W TTT
 H272ICAT: 26W TTT
 H272RICAT: 26W TTT
 H273ICAT1D: 26W TTT
 H273RICAT1D: 26W TTT

DIMENSIONS: OD: 7-1/4" [184mm]


ERT770 Reflector



ERT770MTS Gloss White Trim Ring, Matte Haze Reflector



ERT770TS Gloss White Trim Ring, Clear Specular Reflector



HOUSING / LAMP:

H270ICAT: 13W DTT or 13W TTT
 H270RICAT: 13W DTT or 13W TTT
 H271ICAT: 18W DTT or 18W TTT
 H271RICAT: 18W DTT or 18W TTT
 H272ICAT: 26W DTT or 26W TTT
 H272RICAT: 26W DTT or 26W TTT
 H273ICAT1D: 26W DTT or 26W TTT, 32W TTT
 H273RICAT1D: 26W DTT or 26W TTT, 32W TTT

DIMENSIONS: Height: 5-3/8" [127mm]; OD: 7-1/4" [184mm]

ERT771 Reflector



ERT771TS Gloss White Trim Ring and Gloss White Reflector



HOUSING / LAMP:

H270ICAT: 13W DTT or 13W TTT
 H270RICAT: 13W DTT or 13W TTT
 H271ICAT: 18W DTT or 18W TTT
 H271RICAT: 18W DTT or 18W TTT
 H272ICAT: 26W DTT or 26W TTT
 H272RICAT: 26W DTT or 26W TTT
 H273ICAT1D: 26W DTT or 26W TTT, 32W TTT
 H273RICAT1D: 26W DTT or 26W TTT, 32W TTT

DIMENSIONS: Height: 5" [127mm]; OD: 7-1/4" [184mm]


ERT772 Baffle with Reflector



ERT772WHHTS Gloss White Trim and Baffle with White Reflector, Torsion Spring



ERT772TS Gloss White Trim, Black Baffle, Torsion Spring



HOUSING / LAMP:


H270ICAT: 13W DTT or 13W TTT
 H270RICAT: 13W DTT or 13W TTT
 H271ICAT: 18W DTT or 18W TTT
 H271RICAT: 18W DTT or 18W TTT
 H272ICAT: 26W DTT or 26W TTT
 H272RICAT: 26W DTT or 26W TTT
 H273ICAT1D: 26W DTT or 26W TTT, 32W TTT
 H273RICAT1D: 26W DTT or 26W TTT, 32W TTT

DIMENSIONS: Height: 5-3/8" [127mm]; OD: 7-3/4" [197mm]

ERT724 Drop Opal Lens Showerlight



ERT724 Gloss White Trim with Drop Opal Glass Lens, Wet Location Listed



HOUSING / LAMP:

H270ICAT: 13W DTT or 13W TTT
 H271ICAT: 18W DTT or 18W TTT
 H271RICAT: 18W DTT or 18W TTT
 H272ICAT: 26W DTT or 26W TTT
 H272RICAT: 26W DTT or 26W TTT
 H273ICAT1D: 26W DTT or 26W TTT, 32W TTT
 H273RICAT1D: 26W DTT or 26W TTT, 32W TTT
 H270RICAT: 13W DTT or 13W TTT

DIMENSIONS: Height: 1-11/16 [43mm]; OD: 5-1/64" [129mm]

Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Representative or visit www.cooperlighting.com for available options, accessories and ordering information.