



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 48270371 Flat Boring Bit 3/8" X 6"

*Milwaukee Electric Tool*

Catalog Number	48270371
Manufacturer	Milwaukee Electric Tool
Description	Bore Small, Clean Holes At Any Angle In A Variety Of Materials With The Economical Milwaukee® 3/8 In. X 6 In. Flat Boring Bit. This Premium Quality Flat Boring Bit Is Made Of Heat-Treated High Carbon Steel, So The Drill Point and Cutting Edge Can Be Resharpener For Cost Savings and Long Life. Bore Clean, Fast Holes At Any Angle In Wood, Plastic, Plywood and Formica. This Bit Offers A 6 In. Drilling Depth But Can Be Used With A 12 In. Extension (48-28-3350) For Extended Deep-Hole Drilling. 3/16 In. Shank Di
Weight per unit	0.1000 (lbs/each)
Product Category	Bits, Parts, Accessories

### Features

Flute Length	6
Material	Heat-Treated High-Carbon Steel
Shank Diameter	0.25

### Dimensions and Weight

Length	6.0625
Overall Length	6-1/16



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	FLAT BORING BIT 3/8" X 6"
extra long description	MILW 48-27-0371 Flat Boring Bit
Features	MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening,
Long Description	Bore small, clean holes at any angle in a variety of materials with the economical Milwaukee® 3/8 in. x 6 in. flat boring bit. This premium quality flat boring bit is made of heat-treated high carbon steel, so the drill point and cutting edge can be resharpened for cost savings and long life. Bore clean, fast holes at any angle in wood, plastic, plywood and Formica. This bit offers a 6 in. drilling depth but can be used with a 12 in. extension (48-28-3350) for extended deep-hole drilling. 3/16 in. shank di
Product Type	Flat Boring Bit
Short Description	Flat Boring Bt
Special Features	3/8 IN Bit Diameter; 1/4 IN Shank Diameter; 6-1/16 IN Overall Length; Drill Point And Cutting Edges Can Be Resharpened

## Manufacturer Information

Brand	Milwaukee®
GTIN	00045242120604
Manufacturers Part Number	48-27-0371
UPC	045242120604

## Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	STUBBY

## Packaging

Carton	1
Package	240
Weight Per each	0.1

## Uses, Certifications, and Standards

Application	For Bores Clean Holes At Any Angle In Wood, Plastic, Plywood And Formica
-------------	--