



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



483612SD Encl 48X36X12 N4 SLD DR HC, QTR TRN LTCH *Cooper B-Line/Cable Tray*

Catalog Number	483612SD
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 48" Height, 12" Length, 36" Width, Nema 4, Hinged Cover, SD Enclosure, Wall Mount, Medium Single Door, Thru Holes, Optional External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	120.7 (lbs/each)
Product Category	Nema Types 4 & 12 Metallic Enc

Features

dimensions	12.0000 IN X 36.0000 IN X 48.0000 IN
Material	Carbon Steel
Mounting Type	Wall

Material, Color, and Finish

Color	ANSI 61 GRAY
-------	--------------

Dimensions and Weight

Size	36.00 In Width X 12.00 In Depth X 48.00 In Height
------	---

Descriptions

Description	ENCL 48X36X12 N4 SLD DR HC,QTR TRN LTCH
extra long description	B-LINE 483612-SD TYPE 4/12 SGL SOLI
Features	Eaton's B-Line series wall mounted panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments.
Long Description	Eaton B-Line series wall mounted panel enclosure,48" height,12" length,36" width,NEMA 4,Hinged cover,SD enclosure,Wall mount,Medium single door,Thru holes,optional external mounting feet,Carbon steel,Seamless poured in-place gasket
Product Type	Type 4/12 SGL Solid Door Enc, 48X36X12
Special Features	1/4 turn with 3-pt latching

Manufacturer Information

Brand	Eaton
GTIN	00782051092110
Manufacturers Part Number	483612-SD
UPC	782051092110

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Wall mounted panel enclosure



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	120.671

Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative Energy Datacenters - IT Space: CI and Hyper Converged Commercial / Institutional Buildings / Structures - Building Automation and Monitoring Commercial / Institutional Buildings / Structures - Safety and Security Systems Other IT and Datacom - IT and Datacomm - Other Utility - Substations, Utility Transmission and Distribution Commercial / Institutional Buildings / Structures - Lighting and Lighting Controls Commercial / Institutional Buildings / Structures - Commercial
Mounting	WALL
nema rating	4
standard	CSA C22.2, UL 50, NEMA