



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 48404070 5-3/8" Metal/Stainless Cutting Circular Saw Blade

Milwaukee Electric Tool

Catalog Number	48404070
Manufacturer	Milwaukee Electric Tool
Description	Milwaukee Metal Circular Saw Blades Were Specifically Designed to Exceed The Expectations Of Contractors For Blade Life, Cut Quality, and Speed In The Most Demanding Metal Cutting Applications – Without A Lubricant. A Hand-Tensioned, Hardened Alloy Steel Body Extends Blade Life and Delivers The Highest Quality Cuts Available. Carbide Tipped Teeth With Alternate Top Bevel Grind Shear Through Metal Leaving Burr-Free, Cool-to-Touch Cuts. Designed For Use With The M18™ Cordless 5-3/8 In. Metal Saw, These Blade
Weight per unit	0.4000 (lbs/each)
Product Category	Bits, Parts, Accessories

### Features

Blade Diameter	5 3/8
idea granular category code	1157

### Dimensions and Weight

Size	5-3/8
------	-------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	5-3/8" METAL/STAINLESS CUTTING CIRCULAR SAW BLADE
extra long description	MILW 48-40-4070 5-3/8 in. Circular
Features	5-3/8 in. 30T Ferrous Metal Circular Saw Blade
Long Description	Milwaukee metal circular saw blades were specifically designed to exceed the expectations of contractors for blade life, cut quality, and speed in the most demanding metal cutting applications – without a lubricant. A hand-tensioned, hardened alloy steel body extends blade life and delivers the highest quality cuts available. Carbide tipped teeth with alternate top bevel grind shear through metal leaving burr-free, cool-to-touch cuts. Designed for use with the M18™ cordless 5-3/8 in. metal saw, these blade
Product Type	5-3/8 In. Circular Saw Blade
Short Description	5-3/8 in. Circular Saw Blade
Special Features	Dry - no lubricant required, saving time and money with less mess; Cool - no extreme heat buildup preserves blade life and allows handling the work piece immediately; Clean - no burrs eliminates secondary operations saving time and money; Lasts up to 25x longer than abrasive blades; A hand-tensioned, hardened alloy steel body extends blade life and delivers the highest quality cuts available; Carbide tipped teeth with Alternate Top Bevel grind shear through metal leaving burr-free, cool-to-touch cuts; Thin

## Manufacturer Information

Brand	Milwaukee®
GTIN	00045242233786
Manufacturers Part Number	48-40-4070
UPC	045242233786

## Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	Circular Saw Blade

## Packaging

Carton	1
Weight Per each	0.4

## Uses, Certifications, and Standards

Application	Metal
-------------	-------