



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



48892725 19/64" Thunderbolt Black Oxide Drill Bit *Milwaukee Electric Tool*

Catalog Number	48892725
Manufacturer	Milwaukee Electric Tool
Description	Milwaukee® Thunderbolt® Black Oxide Jobber Length Drill Bits Are Designed For Extreme Durability and Long Life. The Thunderbolt® Web Features A Thicker Core Than A Standard Drill Bit, Which Provides Ultimate Strength and Protects Against Side-Load Breakage. A Specially Designed Parabolic Flute Form Clears Chips and Debris Fast to Keep The Bit Cool. A Precision Start, 135 Split Point Tip Starts On Contact to Keep The Bit From Walking For Fast Accurate Holes. Excellent For Drilling On Curved Surfaces, Requir
Weight per unit	0.0750 (lbs/each)
Product Category	Bits, Parts, Accessories

Features

Drill Diameter	0.297
Flute Length	4.0
package quantity	1
Shank Diameter	0.25

Dimensions and Weight

Length	6.0
--------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	19/64" THUNDERBOLT BLACK OXIDE DRILL BIT
extra long description	MILW 48-89-2725 19/64" Thunderbolt
Features	MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening,
Long Description	Milwaukee® Thunderbolt® Black Oxide Jobber length drill bits are designed for extreme durability and long life. The Thunderbolt® web features a thicker core than a standard drill bit, which provides ultimate strength and protects against side-load breakage. A specially designed parabolic flute form clears chips and debris fast to keep the bit cool. A precision start, 135 Split Point tip starts on contact to keep the bit from walking for fast accurate holes. Excellent for drilling on curved surfaces, requir
Product Type	19/64" Thunderbolt Black Oxide

Manufacturer Information

Brand	Milwaukee®
GTIN	00045242166947
Manufacturers Part Number	48-89-2725
series	Milwaukee® Thunderbolt® Black Oxide
UPC	045242166947

Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
----------------------	-----------------------------

Packaging

Carton	1
Package	195
Weight	0.075
Weight Per each	0.075