



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



48892727 21/64" Thunderbolt Black Oxide Drill Bit

Milwaukee Electric Tool

| | |
|------------------|---|
| Catalog Number | 48892727 |
| Manufacturer | Milwaukee Electric Tool |
| Description | Milwaukee® Thunderbolt® Black Oxide Jobber Length Drill Bits Are Designed For Extreme Durability and Long Life. The Thunderbolt® Web Features A Thicker Core Than A Standard Drill Bit, Which Provides Ultimate Strength and Protects Against Side-Load Breakage. A Specially Designed Parabolic Flute Form Clears Chips and Debris Fast to Keep The Bit Cool. A Precision Start, 135 Split Point Tip Starts On Contact to Keep The Bit From Walking For Fast Accurate Holes. Excellent For Drilling On Curved Surfaces, Requir |
| Weight per unit | 0.0850 (lbs/each) |
| Product Category | Bits, Parts, Accessories |

Features

| | |
|------------------|----------|
| Drill Diameter | 0.3280 |
| Flute Length | 4.000000 |
| package quantity | 1 |
| Shank Diameter | 0.250000 |

Dimensions and Weight

| | |
|--------|-----|
| Length | 6.0 |
|--------|-----|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 21/64" THUNDERBOLT BLACK OXIDE DRILL BIT |
| extra long description | MILW 48-89-2727 21/64" Thunderbolt |
| Features | MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening, |
| Long Description | Milwaukee® Thunderbolt® Black Oxide Jobber length drill bits are designed for extreme durability and long life. The Thunderbolt® web features a thicker core than a standard drill bit, which provides ultimate strength and protects against side-load breakage. A specially designed parabolic flute form clears chips and debris fast to keep the bit cool. A precision start, 135 Split Point tip starts on contact to keep the bit from walking for fast accurate holes. Excellent for drilling on curved surfaces, requir |
| Product Type | 21/64" Thunderbolt Black Oxide |

Manufacturer Information

| | |
|---------------------------|-------------------------------------|
| Brand | Milwaukee® |
| GTIN | 00045242166985 |
| Manufacturers Part Number | 48-89-2727 |
| series | Milwaukee® Thunderbolt® Black Oxide |
| UPC | 045242166985 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------|
| Category Description | BITS, BLADES, AND HOLE SAWS |
|----------------------|-----------------------------|

Packaging

| | |
|-----------------|----------|
| Carton | 1 |
| Weight | 0.090000 |
| Weight Per each | 0.085 |