



M18 REDLITHIUM™

THE WORLD'S FIRST & ONLY 18V HIGH DEMAND™ 9.0 BATTERY

[Learn More](#)

Swap Banner



Thunderbolt® Black Oxide Drill Bit Set (21 PC)

48-89-2801



What's Included

- (2) 1/16" Thunderbolt Black Oxide Drill Bit
- (1) 11/64" Thunderbolt Black Oxide Drill Bit
- (1) 1/2" Thunderbolt Black Oxide Drill Bit
- (1) 13/64" Thunderbolt Black Oxide Drill Bit
- (2) 1/4" Thunderbolt Black Oxide Drill Bit
- (1) 15/64" Thunderbolt Black Oxide Drill Bit
- (2) 1/8" Thunderbolt Black Oxide Drill Bit
- (2) 3/16" Thunderbolt Black Oxide Drill Bit
- (1) 3/32" Thunderbolt Black Oxide Drill Bit
- (1) 3/8" Thunderbolt Black Oxide Drill Bit
- (1) 5/16" Thunderbolt Black Oxide Drill Bit
- (1) 5/32" Thunderbolt Black Oxide Drill Bit
- (2) 5/64" Thunderbolt Black Oxide Drill Bit
- (1) 7/32" Thunderbolt Black Oxide Drill Bit
- (1) 7/64" Thunderbolt Black Oxide Drill Bit
- (1) 9/64" Thunderbolt Black Oxide Drill Bit

Where to Buy

- Shop Online
- Find Local

Specifications

Coating	Black Oxide
----------------	-------------

Features

- Extreme durability: Thicker web provides greater strength and longer life
- Fast, accurate drilling: 135° split point tip starts on contact to prevent walking, while the parabolic flute clears chips fast
- Reduced slipping: 3-Flat Secure-Grip™ shank holds the bit firmly in the drill chuck
- Corrosion resistant: Black coating provides lubricity and resists corrosion of the bit

Overview

The 21-Piece Thunderbolt® Black Oxide Drill Bit Set offers convenience and heavy-duty performance on the jobsite. Milwaukee® Thunderbolt Black Oxide drill bits are designed for extreme durability and long life. The Thunderbolt web features a thicker core than a standard drill bit to provide ultimate strength and protect against side-load breakage. A specially designed parabolic flute form clears chips fast, while the 3-Flat Secure-Grip™ shank holds the bit firmly in the drill chuck. The 135° split point tip delivers a precision start and prevents walking for fast, accurate holes. Effective for drilling on curved surfaces, Milwaukee Thunderbolt Black Oxide bits require less effort to drill through metal, wood and PVC, and are highly recommended for use with portable drills. The set comes in a resilient case and includes bit sizes (2) 1/16", (2) 5/64", 3/32", 7/64", (2) 1/8", 9/64", 5/32", 11/64", (2) 3/16", 13/64", 7/32", 15/64", (2) 1/4", 5/16", 3/8", and 1/2".

Model Options

Item/Cat #	
48-89-2803	Shop Online Find Local
Thunderbolt® Black Oxide Drill Bit Set (21 PC) 48-89-2801	Shop Online Find Local
48-89-2802	Shop Online Find Local

© 2016 by Milwaukee Tool. All rights reserved.