



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



49251251 Open-Lok 1-1/8" Titanium Enhanced Bi-Metal Blade

Milwaukee Electric Tool

Catalog Number	49251251
Manufacturer	Milwaukee Electric Tool
Description	The Milwaukee® Open-Lok™ 1-1/8" Titanium Charged™ Bi-Metal Thin Metal Oscillating Multi-Tool Blades Are Made From Premium High-Speed Steel. These Bi-Metal Blades Are Ideal For Cuts In Thin Metal, Nails, PVC, and Drywall. Titanium Charged™ Bi-Metal Blades Have An Optimized Titanium Blend For Maximum Wear-Resistance and Up to 15X Longer Life VS. High Carbon Steel (HCS) Blades. These Blades Feature A Reinforced Universal Fit Open-Lok™ Anchor For Better Strength & Control and Allow For Quick Blade Changes Acro
Weight per unit	0.0800 (lbs/each)
Product Category	Tools & Testers

Features

Blade Length	2.2
Blade Thickness	0.03
Blade Width	1.125

Material, Color, and Finish

Blade Material	Bi-Metal
----------------	----------

Dimensions and Weight

Size	1-1/8
------	-------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	OPEN-LOK 1-1/8" TITANIUM ENHANCED BI-METAL BLADE
extra long description	MILW 49-25-1251 1-1/8" TITANIUM BI-
Features	MILWAUKEE® Oscillating Multi-Tool Accessories provide a complete solution for cutting, scraping, sanding and grinding across a wide range of materials and applications. Equipped with an OPEN-LOK™ Universal blade anchor for quick blade changes. Made with high quality materials and advanced manufacturing processes to deliver professional grade performance and market leading innovation.
Long Description	The MILWAUKEE® OPEN-LOK™ 1-1/8" TITANIUM CHARGED™ Bi-Metal Thin Metal Oscillating Multi-Tool Blades are made from premium high-speed steel. These bi-metal blades are ideal for cuts in thin metal, nails, PVC, and drywall. TITANIUM CHARGED™ Bi-Metal blades have an optimized titanium blend for maximum wear-resistance and up to 15x longer life vs. high carbon steel (HCS) blades. These blades feature a reinforced Universal Fit OPEN-LOK™ anchor for better strength & control and allow for quick blade changes acro
Product Type	1-1/8" Titanium Bi-Metal Blade 1PK
Short Description	1-1/8" Titanm BI-METAL Bid 1PK

Manufacturer Information

Brand	Milwaukee®
GTIN	00045242571024
Manufacturers Part Number	49-25-1251
UPC	045242571024

Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	Multi-Tool Blade

Packaging

Carton	1
Package	4
Weight Per each	0.08

Uses, Certifications, and Standards

Application	Metal
-------------	-------