



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 48899284 Cobalt Step Drill Bit #4 (3/16-7/8")

*Milwaukee Electric Tool*

Catalog Number	48899284
Manufacturer	Milwaukee Electric Tool
Description	The Milwaukee® #4 Cobalt Step Drill Bits Are Engineered to Deliver Up to 15X The Life In Stainless Compared to Current Solutions and Up to 1000 Holes In Mild Steel. The Cobalt Step Drill Bits Are Recommended Up to 14GA. The Elongated Dual-Flute Design Also Offers The Best Heat Management Combined With The Smaller Steps For Smoothest Drilling Experience and A Rapid Strike™ Tip That Allows For 2X Faster Starts In Stainless. Made In The Usa With Global Materials, These Step Bits Have Best-In-Class Performance
Weight per unit	0.2300 (lbs/each)
Product Category	Tools & Testers

### Features

Flute Length	2.78
Shank Diameter	0.375

### Dimensions and Weight

Length	3.65
--------	------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	COBALT STEP DRILL BIT #4 (3/16-7/8")
extra long description	MILW 48-89-9284 Milwaukee Cobalt St
Features	MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening,
Long Description	The MILWAUKEE® #4 Cobalt Step Drill Bits are engineered to deliver up to 15X the life in stainless compared to current solutions and up to 1000 holes in mild steel. The Cobalt Step Drill Bits are recommended up to 14ga. The elongated dual-flute design also offers the best heat management combined with the smaller steps for smoothest drilling experience and a Rapid Strike™ tip that allows for 2X faster starts in stainless. Made in the USA with global materials, these step bits have best-in-class performance
Product Type	Milwaukee Cobalt Step Drill Bit #4
Short Description	Cobalt Step Drill Bt #4

## Manufacturer Information

Brand	Milwaukee®
GTIN	00045242567614
Manufacturers Part Number	48-89-9284
UPC	045242567614

## Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
----------------------	-----------------------------

## Packaging

Carton	1
Weight Per each	0.23