



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 4BEMWSWW590CRIM6 4" Recessed Led Trim 27/30/35/40/50K 700LM *Lithonia Lighting*

Catalog Number	4BEMWSWW590CRIM6
Manufacturer	Lithonia Lighting
Description	The E Series Led Recessed Module Gives You Optimized Value and Performance You Can Trust. The E Series Combines Dependable Performance and Low Cost With The Virtually Maintenance-Free, Energy-Saving Benefits Of A 54, 000 Hour Rated-Life Led. Ideal For Both Retrofitting and New Construction In A Variety Of Residential and Light Commercial Settings Such As Multifamily Residences, Retail Shops and Offices. The 4" E Series Fits 4-Inch Recessed Can-Style Housings Using Friction Clips and Can Replace A 65W Incand
Weight per unit	0.7000 (lbs/each)
Product Category	Lighting

### Features

average life	50,000
dimensions	5.25 x 5.25 x 3.17
dimnable	Yes
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Dynamic
lumens	700 LM
Material	Aluminum
media	Yes
Number of Lamps	1
Shape	Round
Voltage Rating	120 V
Warranty	5
Wattage	8.6

### Material, Color, and Finish

Color	White
Finish	Matte
Style	CONTEMPORARY

### Dimensions and Weight

Height	3.42
Length	5.23
Width	5.23



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Construction	Retrofit
Description	4" RECESSED LED TRIM 27/30/35/40/50K 700LM
extra long description	LITH 4BEMW SWW5 90CRI M6 4IN Juno E
Features	Design Select
Long Description	The E Series LED Recessed Module gives you optimized value and performance you can trust. The E Series combines dependable performance and low cost with the virtually maintenance-free, energy-saving benefits of a 54,000 hour rated-life LED. Ideal for both retrofitting and new construction in a variety of residential and light commercial settings such as multifamily residences, retail shops and offices. The 4" E Series fits 4-inch recessed can-style housings using friction clips and can replace a 65W incand
Product Type	Trim

## Manufacturer Information

Brand	JUNO
GTIN	00194994160519
Manufacturers Part Number	4BEMW SWW5 90CRI M6
UPC	194994160519

## Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Trim

## Trade Size

aperture size	4 in
---------------	------

## Packaging

Carton	1
Package	6
Weight Per each	0.7

## Uses, Certifications, and Standards

Application	Hospitality,Residential,Retail,Retrofit
environmental conditions	Indoor,Outdoor
Mounting	Recessed
standard	CSAus,NOMCA Title 20,CA Title 24,ENERGY STAR,JA8