



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



4RLDG409LM30K90C 4" Led Adj Retro 30K 4900 LM 120V 90cri

Lithonia Lighting - Acuity

Catalog Number	4RLDG409LM30K90C
Manufacturer	Lithonia Lighting - Acuity
Description	With Juno Retrofit 3000K Warm White Led Retrofit Downlight RLD 4-Inch Trim Modules, Upgrading Your Existing 4-Inch Recessed Fixture Is Inexpensive and Nearly As Simple As Replacing An Incandescent Lamp. Modules Feature A White Aluminum Baffle With A Built-In Flange. A Deeply Regressed Diffusing Lens Conceals The Leds From Direct View and Provides Uniform Aperture Luminance.
Weight per unit	0.9000 (lbs/each)
Product Category	Lighting

Features

average life	50,000
dimensions	5.0 x 5.0 x 2.0
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Static
lumens	900 lm
Material	Aluminum
Maximum Operating Temperature	25
Number of Lamps	1
Power Source	Plug-In
Shape	Round
Voltage Rating	120
Warranty	5
Wattage	12

Material, Color, and Finish

Color	White
color rendering index (cri)	90
color temperature	3000
Lens Color	WHITE
Lens Material	Polycarbonate

Dimensions and Weight

Height	2.88
Length	5.06
Width	5.06



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Construction	Retrofit
Description	4" LED ADJ RETRO 30K 4900 LM 120V 90CRI
extra long description	LITH 4RLD G4 09LM 30K 90CRI 120 FRP
Features	Contractor Select
Long Description	With Juno Retrofit 3000K Warm White LED Retrofit Downlight RLD 4-inch trim modules, upgrading your existing 4-inch recessed fixture is inexpensive and nearly as simple as replacing an incandescent lamp. Modules feature a white aluminum baffle with a built-in flange. A deeply regressed diffusing lens conceals the LEDs from direct view and provides uniform aperture luminance.
Product Type	Trim

Manufacturer Information

Brand	JUNO
GTIN	00194994892854
Manufacturers Part Number	4RLD G4 09LM 30K 90CRI 120 FRP
UPC	194994892854

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Trim

Trade Size

aperture size	4 in
---------------	------

Packaging

Carton	1
Package	6
Weight	0.66
Weight Per each	0.9

Uses, Certifications, and Standards

Application	Healthcare,Residential,Retrofit
environmental conditions	Indoor
Mounting	Recessed
standard	cULus ClassifiedCA Title 20,CA Title 24,ENERGY STAR,JA8