



## ADJUSTABLE T-GRID BOX HANGER, 24" T-GRID SPAN

### CATALOG NUMBER

---

**512A**



### FEATURES

---

Adjustable height allows installation of double deep boxes, speaker cases and emergency light fixtures above T-Grid

Snaps easily onto T-Grid

Hanger comes complete with box mounting clip and screw

### PRODUCT ATTRIBUTES

---

Material: Steel;Spring Steel

Finish: Pregalvanized;nVent CADDY Armour

T-Grid Span: 24"

Height: 8" Max

Ultimate Static Load: 20lb

### ADDITIONAL PRODUCT DETAILS

---

Not to exceed static load without independent wire support to box mounting clip.

Not permitted for paddle fans.

### WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**  
+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

**Europe**  
Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**  
Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**  
Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**



## ADJUSTABLE T-GRID BOX HANGER, 24" T-GRID SPAN

### CATALOG NUMBER

---

**512A**



### FEATURES

---

Adjustable height allows installation of double deep boxes, speaker cases and emergency light fixtures above T-Grid

Snaps easily onto T-Grid

Hanger comes complete with box mounting clip and screw

### PRODUCT ATTRIBUTES

---

Material: Steel;Spring Steel

Finish: Pregalvanized;nVent CADDY Armour

T-Grid Span: 24"

Height: 8" Max

Ultimate Static Load: 20lb

### ADDITIONAL PRODUCT DETAILS

---

Not to exceed static load without independent wire support to box mounting clip.

Not permitted for paddle fans.

### WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**  
+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

**Europe**  
Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**  
Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**  
Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**