

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301480083](#)
Status: **Active**
Overview: [Heavy-Duty Industrial Wiring Devices](#)
Description: Safeway Duplex Heavy - Duty Spec - Grade Receptacle, 2 Pole/3 Wire, NEMA 5-15, 125V, Brown

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E46237

General

Product Family Wiring Devices
 Series [130148](#)
 IP Rating N/A
 NEMA Configuration NEMA 5-15
 Overview [Heavy-Duty Industrial Wiring Devices](#)
 Product Literature Order No 987650-8068
 Product Name Safeway
 Receptacle Type Duplex
 Specialty N/A
 Type Receptacle
 UPC 78678871864
 Woodhead Yes

Physical


Flange No
 Flip Lid No
 Gender Female
 Length N/A
 Locking Blade No
 Net Weight 84.821/g
 Poles 2-pole/3-wire

Electrical

Cord Type N/A
 Current - Maximum per Contact 15.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 125V

Material Info

Engineering Number 5262DW



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130148 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301480083](#)
Status: **Active**
Overview: [Heavy-Duty Industrial Wiring Devices](#)
Description: Safeway Duplex Heavy - Duty Spec - Grade Receptacle, 2 Pole/3 Wire, NEMA 5-15, 125V, Brown

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E46237

General

Product Family Wiring Devices
 Series [130148](#)
 IP Rating N/A
 NEMA Configuration NEMA 5-15
 Overview [Heavy-Duty Industrial Wiring Devices](#)
 Product Literature Order No 987650-8068
 Product Name Safeway
 Receptacle Type Duplex
 Specialty N/A
 Type Receptacle
 UPC 78678871864
 Woodhead Yes

Physical


Flange No
 Flip Lid No
 Gender Female
 Length N/A
 Locking Blade No
 Net Weight 84.821/g
 Poles 2-pole/3-wire

Electrical

Cord Type N/A
 Current - Maximum per Contact 15.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 125V

Material Info

Engineering Number 5262DW



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130148 Series](#)