



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



55808701 Sjoow 12/3 Black 250' Southwire Company

Catalog Number	55808701
Manufacturer	Southwire Company
Description	Southwire Type Sjoow Flexible Cords UI/ Csa Listed Are Permitted For Use As Specified By Article 400 and Related Articles Of The 2014 National Electrical Code. The Cable Is Rated -40°C to 90°C, Water, Oil, and Weather Resistant, Designed For Hard Usage On Industrial Equipment, Heavy Tools, Battery Chargers, Portable Lights Welding Leads, Marine Dockside Power, Power Extensions and Mining Applications.
Weight per unit	1.0 (lbs/ft)
Product Category	Wire

Features

Conductor Size	12
connector	N/A
core	12
insulation	EPDM
media	Yes
Number of Conductors	3
Number of Outlets	N/A
outside diameter	0.435
Plug Type	N/A
strands	65
Voltage Rating	300

Material, Color, and Finish

Color	Black
Conductor Material	Copper

Dimensions and Weight

Length	250
--------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Construction	CPE JACKET
Description	SJOOW 12/3 BLACK 250'
extra long description	SWC 55808701 12-65 2/C CU SJOOW BLA
Long Description	Southwire Type SJOOW Flexible Cords UL/ CSA listed are permitted for use as specified by Article 400 and related articles of the 2014 National Electrical Code. The cable is rated -40°C to 90°C, water, oil, and weather resistant, designed for hard usage on industrial equipment, heavy tools, battery chargers, portable lights welding leads, marine dockside power, power extensions and mining applications.
Product Type	12-65 2/C Cu Sjoow Black 90(D)C 300V UI/Csa

Manufacturer Information

Brand	Copper
GTIN	00032886081095
Manufacturers Part Number	55808701
UPC	032886081095

Taxonomies, Classifications, and Categories

Type	SJOOW
------	-------

Packaging

Carton	1
Weight	35.05
Weight Per foot	1

Uses, Certifications, and Standards

Application	FLEXCORD
standard	UL62