


MULTI-GROOVE FIBERGLASS FISH TAPES



**MULTI-GROOVE
TECHNOLOGY**



**Low Friction,
Easy Feed Design**

**Fiberglass Performance
at 25% Lower Cost!***

**KLEIN
TOOLS** 

For Professionals... Since 1857[®] USA

Multi-Groove Fiberglass Fish Tapes

Fiberglass Performance

*at 25% Lower Cost!**




MULTI-GROOVE TECHNOLOGY

Low friction,
easy feed design



OLD PROFILE



NEW PROFILE



Less surface contact with wires


Fiberglass core and grooves provide:

- Rigidity for long distance.
- Less surface contact when pushing through crowded conduit.

TWO TIP OPTIONS

Multi-Groove Fiberglass Fish Tapes – 7" Spiral Steel Leader

Cat. No.	UPC# 0-92644+	Tape Size	Reel Diameter	Weight
56055	56055-2	100'L x 3/16"W (7"leader)	13" (330 mm)	3.09 lbs.
56056	56056-9	200'L x 3/16"W (7"leader)	17" (432 mm)	6.16 lbs.



Multi-Groove Fiberglass Fish Tapes – Non-Conductive

Cat. No.	UPC# 0-92644+	Tape Size	Reel Diameter	Weight
56057	56057-6	50'L x 3/16"W	13" (330 mm)	2.33 lbs.
56058	56058-3	100'L x 3/16"W	13" (330 mm)	3.05 lbs.
56059	56059-0	200'L x 3/16"W	17" (432 mm)	6.04 lbs.




WARNING: Never remove screws while fish tape is coiled inside reel.



* When compared to published price of Klein Tools round fiberglass fish tapes.

MULTI-GROOVE FIBERGLASS FISH TAPES



**MULTI-GROOVE
TECHNOLOGY**



**Low Friction,
Easy Feed Design**

**Fiberglass Performance
at 25% Lower Cost!***

**KLEIN
TOOLS** 

For Professionals... Since 1857[®] USA

Multi-Groove Fiberglass Fish Tapes

Fiberglass Performance

at 25% Lower Cost!*




MULTI-GROOVE TECHNOLOGY

**Low friction,
easy feed design**



OLD PROFILE



NEW PROFILE



**Less surface contact
with wires**


Fiberglass core and grooves provide:

- Rigidity for long distance.
- Less surface contact when pushing through crowded conduit.

TWO TIP OPTIONS

Multi-Groove Fiberglass Fish Tapes – 7" Spiral Steel Leader

Cat. No.	UPC# 0-92644+	Tape Size	Reel Diameter	Weight
56055	56055-2	100'L x 3/16"W (7"leader)	13" (330 mm)	3.09 lbs.
56056	56056-9	200'L x 3/16"W (7"leader)	17" (432 mm)	6.16 lbs.



Multi-Groove Fiberglass Fish Tapes – Non-Conductive

Cat. No.	UPC# 0-92644+	Tape Size	Reel Diameter	Weight
56057	56057-6	50'L x 3/16"W	13" (330 mm)	2.33 lbs.
56058	56058-3	100'L x 3/16"W	13" (330 mm)	3.05 lbs.
56059	56059-0	200'L x 3/16"W	17" (432 mm)	6.04 lbs.



⚠WARNING: Never remove screws while fish tape is coiled inside reel.



* When compared to published price of Klein Tools round fiberglass fish tapes.