



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 6100US 1" MT Coupling *Appleton/Oz Gedney*

Catalog Number	6100US
Manufacturer	Appleton/Oz Gedney
Description	Emt Couplings, Etp Compression, Series: 6000US, Material: Steel/Zinc Plated, Trade Size: 1, Body Length: 1.41", Maximum Diameter: 1.50", UI Standard: 514B, UI Listed: (1/2-3) E14815, Csa Standard: C22.2 No. 18.3, Cul Listed: (1/2-3) E14815, Nema: FB-1
Weight per unit	0.3500 (lbs/each)
Product Category	Steel Compression Emt CPLG

### Features

Connector Type	Compression
Material	Steel

### Material, Color, and Finish

Color	Metallic
-------	----------

### Dimensions and Weight

Length	1.41
--------	------

### Descriptions

Description	1" MT COUPLING
extra long description	EGS 6100US 1 IN EMT COMP CPLG USA
Long Description	EMT Couplings, ETP Compression, Series: 6000US, Material: Steel/zinc plated, Trade size: 1, Body Length: 1.41", Maximum Diameter: 1.50", UL Standard: 514B, UL Listed: (1/2-3) E14815, CSA Standard: C22.2 No. 18.3, cUL Listed: (1/2-3) E14815, NEMA: FB-1
Product Type	1 In Emt Comp CPLG Usa
Special Features	1 IN Compression Coupling, Made in USA, Concretetight, Raintight (wet locations) Canada

### Manufacturer Information

Brand	Appleton
GTIN	00687855050321
Manufacturers Part Number	6100US
UPC	687855050321

### Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	EMT Conduit Compression Coupling



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Trade Size

Trade Size ..... 1

## Packaging

Carton ..... 20

Package ..... 100

Weight Per each ..... 0.35

## Uses, Certifications, and Standards

Application ..... To ground and secure EMT raceway sections together in wet locations

standard ..... UL Standard: 514B; UL Listed: E14815, E14895; CSA Standard: C22.2 No. 18.3, cUL Listed: E14815; CSA Certified: 028507; NEMA: FB-1