



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

63501 11" 7W Led Undercab 3K/4K/5K White

Satco



Catalog Number	63501
Manufacturer	Satco
Description	6.5 Watt 11-Inch Led White Under Cabinet Light - CCT Selectable - 40000 Hours
Weight per unit	0.7100 (lbs/each)
Product Category	Lighting

Features

Lamp Type	integrated LED
Material	Aluminum and Polycarbonate (PC)
Warranty	5 Year Limited - Fixtures

Material, Color, and Finish

Finish	white
--------	-------

Dimensions and Weight

Height	1
Length	11
Width	3.5

Descriptions

Description	11" 7W LED UNDERCAB 3K/4K/5K WHITE
extra long description	SATCO 63/501 UNDER CAB LED SCCT 11"
Long Description	6.5 Watt 11-Inch LED White Under Cabinet Light - CCT Selectable - 40000 Hours
Product Type	Under Cab Led SCCT 11" - WH
Special Features	Lumens: 408L-456L ; CCT: 3000K/4000K/5000K ; Color Temperature: Warm to Cool White ; CRI: 90+ ; Dimmable: Yes-Dimmable ; Hours Rated: 40000 ; DLC Approved: No ; Energy Star: Yes ; Warranty: 5 Year Limited - Fixtures ; Brand: CounterQuick ; ADA Compliant: Yes ; Beam Spread: 105 degrees ; CCT Selectable: Yes ; California T24 Compliant ; Incandescent Equivalent: 30W ; Indoor/Outdoor: Indoor ; IP Rating: IP20 ; NSF Approved: No ; Operating Temperature: -20C (-4F) to a maximum of +40C (+104F) ; RoHS Compliant:

Manufacturer Information

Brand	Nuvo
GTIN	00045923656477
Manufacturers Part Number	63/501
UPC	045923656477



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED TRACK, RAIL, TASK & UNDERCABINET LIGHTING
Type	Undercabinet

Packaging

Carton	1
Weight	0.71
Weight Per each	0.71

Uses, Certifications, and Standards

Application	LED Undercabinet
Mounting	Undercabinet
Operating Temperature	-20C (-4F) to a maximum of +40C (+104F)
standard	cETLus