



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



65023000 1/2" LFNC Orange Sealtight *Southwire Company*

Catalog Number	65023000
Manufacturer	Southwire Company
Description	UI Liquidtight Flexible Nonmetallic Conduit, Type LFNC-A, 6500 Series, Liquidtight Flexible Nonmetallic Conduit. Flame Retardant Three Part PVC Construction. Color: Orange, 1/2 Inch Diameter, 100 Foot Carton
Weight per unit	0.1600 (lbs/each)
Product Category	20120105134924

Features

Inside Diameter	0.610/0.650
Material	PVC
outside diameter	0.900/0.940

Material, Color, and Finish

Color	Orange
Finish	PVC
Jacket Material	PVC

Dimensions and Weight

Length	100
--------	-----

Descriptions

Description	1/2" LFNC ORANGE SEALTIGHT
extra long description	AFC 6502-30-00 1/2 UL ORANGE LFNC-A
Features	LIQUID-TUFF™ Type LFNC-A is a layered Liquidtight Flexible Nonmetallic Conduit, designed for use in wet, dry or oily locations as a flame resistant, Nonmetallic raceway for power, control and communications cables where repetitive motion and constant flexing is required. It is intended for applications where abrasion and physical abuse may occur. LIQUID-TUFF™ Type LFNC-A carries the UL Listing Marks for US and Canada
Long Description	UL Liquidtight Flexible Nonmetallic Conduit, Type LFNC-A, 6500 Series, Liquidtight Flexible Nonmetallic Conduit. Flame Retardant Three Part PVC Construction. Color: Orange, 1/2 inch Diameter, 100 Foot Carton
Product Type	1/2 UI Orange LFNC-A 100 CTN
Short Description	1/2 UL ORANGE LFNC-A 100 CTN
Special Features	Nylon reinforced braid between two layers of PVC for strength and flexibility. Sunlight resistant, oil resistant, mild acid resistance, non-conductive raceway.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Flexible Conduit
GTIN	00077680175632
Manufacturers Part Number	6502-30-00
UPC	077680175632

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	Liquidtight Flexible Non-Metallic Conduit

Trade Size

Trade Size	1/2
------------	-----

Packaging

Carton	1
Package	100
Weight	0.16
Weight Per each	0.16

Uses, Certifications, and Standards

Application	Constant flexing and motion applications
standard	UL 1660 E123464
Temperature Rating	176