



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



65686 60 Watt Led Area Light With Photocell - CCT Select

Satco

Catalog Number	65686
Manufacturer	Satco
Description	60 Watt Led Area Light With Photocell - CCT Selectable and Dimmable - Bronze Finish - 120-277 Volts - Ultra Bright Lumens
Weight per unit	7.5 (lbs/each)
Product Category	Lighting

Features

Lamp Type	LED
Material	Aluminum
Number of Lamps	1
surge protection	Built-in surge protection - 4KV
Warranty	5 Year Limited - Fixtures

Material, Color, and Finish

fixture material	aluminum
------------------	----------

Descriptions

Description	60 WATT LED AREA LIGHT WITH PHOTOCCELL - CCT SELECT
extra long description	SATCO 65/686 60W LED AREA LIGHT W/P
Long Description	60 Watt LED Area Light with Photocell - CCT Selectable and Dimmable - Bronze Finish - 120-277 Volts - Ultra Bright Lumens
Product Type	60W Led Area Light W/Photocell Bronze
Special Features	Lawful for sale in California ; Warranty: 5 Year Limited - Fixtures ; Watts: 60 ; Voltage range: 120V-277V ; Lumen range: 8400L-9600L ; CCT: 3000K/4000K/5000K ; CRI: 70 ; Dimmable: Yes-Dimmable ; Dimming type: 1-10V Dimmable ; Hours Rated: 50000 ; DLC approved: Yes ; Notes: Type V Lighting Distribution/ Dusk to Dawn Lamp ; Beam spread: 150x150 ; Flicker free ; HID equivalent: 250W ; Incandescent equivalent: 500W ; IP65 rated ; Operating temperature: -40C (-40F) to a maximum of +50C (+122F) ; Photocell: Yes

Manufacturer Information

Brand	Nuvo
GTIN	00045923656866
Manufacturers Part Number	65/686
UPC	045923656866

Taxonomies, Classifications, and Categories

Category Description	LED TRACK, RAIL, TASK & UNDERCABINET LIGHTING
Type	AREA LIGHT



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight	5.07
Weight Per each	7.5

Uses, Certifications, and Standards

Application	Security Lighting
environmental conditions	Wet location
standard	cULus