



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



65BEMWHLSWW590CR 6" 12W Led Trim 1200LM Color Selectable

Lithonia Lighting - Acuity

| | |
|------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | 65BEMWHLSWW590CR |
| Manufacturer | Lithonia Lighting - Acuity |
| Description | Experience The Ultimate 5-In-1 Solution With E Series Switchable White Led Trim Kits. Offering Flexibility At Your Fingertips, E Series Trim Kits Feature A Switch, Located Directly On The Fixture, That Allows You to Choose Between 5 Color Temperature Options Ranging From 2700K (Warm White) to 5000K (Daylight). Available In 5/6" Size, The E Series Provides Easy Retrofitting From Below The Ceiling or Can Be Paired With A Juno® Quick Connect QC Series Recessed Housing For New Construction Applications. |
| Weight per unit | 0.7000 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-----------------|-----------------------|
| average life | 50,000 |
| dimensions | 7.625 x 7.625 x 3.667 |
| dimnable | Yes |
| Hardware | Yes |
| Lamp Included | Yes |
| Lamp Type | LED - Dynamic |
| lumens | 1200 LM,900 LM |
| Material | Aluminum |
| Number of Lamps | 1 |
| Reflector Type | Aluminum Spun |
| Shape | Round |
| Socket Type | N/A |
| Voltage Rating | 120 V |
| Warranty | 5 |
| Wattage | 13.9 |

Material, Color, and Finish

| | |
|--------|--------------|
| Color | White |
| Finish | Matte |
| Style | CONTEMPORARY |

Dimensions and Weight

| | |
|--------|-------|
| Height | 4.125 |
| Length | 7.625 |
| Width | 7.625 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Construction | Retrofit |
| Description | 6" 12W LED TRIM 1200LM COLOR SELECTABLE |
| extra long description | LITH 65BEMW HL SWW5 90CRI M6 6IN Ju |
| Features | Contractor Select |
| Long Description | Experience the ultimate 5-in-1 solution with E Series Switchable White LED Trim Kits. Offering flexibility at your fingertips, E Series Trim Kits feature a switch, located directly on the fixture, that allows you to choose between 5 color temperature options ranging from 2700K (Warm White) to 5000K (Daylight). Available in 5/6" size, the E Series provides easy retrofitting from below the ceiling or can be paired with a Juno® Quick Connect QC Series recessed housing for new construction applications. |
| Product Type | Trim |
| Special Features | Switchable Color Temperature |

Manufacturer Information

| | |
|---------------------------|-------------------------|
| Brand | JUNO |
| GTIN | 00194994244950 |
| Manufacturers Part Number | 65BEMW HL SWW5 90CRI M6 |
| UPC | 194994244950 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------------------------|
| Category Description | LED ARCHITECTURAL & SPECIFICATION LIGHTING |
| Type | Trim |

Trade Size

| | |
|---------------|-----------|
| aperture size | 5 IN,6 IN |
|---------------|-----------|

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Package | 6 |
| Weight Per each | 0.7 |

Uses, Certifications, and Standards

| | |
|--------------------------|----------------------------------------------|
| Application | Hospitality,Residential,Retail,Retrofit |
| environmental conditions | Indoor,Outdoor |
| Mounting | Recessed |
| standard | CSAusCA Title 20,CA Title 24,ENERGY STAR,JA8 |